


Céliane™ with Netatmo Connected 2P+E socket - French standard

Cat. No(s): 1 991 60/61/70/71/80/81




1. USE

Connected socket which can be controlled by a wireless lighting control and/or remotely via a smartphone, tablet or computer.
Can be used to measure instantaneous and total consumption of the connected device, which can be viewed on the Home + Control app.
Built-in protection against electrical overloads, for increased safety.
Installation in box 40 mm deep (minimum), instead of a standard socket outlet.
Screw and/or claw fixing.
One-piece mechanism (grid + mechanism).

2. RANGE

Description	White	Titanium	Graphite
Connected 2P+E socket with safety shutters. With activity and identification LED indicator and RESET button (hidden) used to return to factory settings. Complete delivered. Supplied with site protection cover.	1 991 61	1 991 71	1 991 81
Extension pack 3 connected 2P+E socket outlets	1 991 60	1 991 70	1 991 80

3. DIMENSIONS (mm)




A	B	C	D
82	90	42	31.5

4. CONNECTION

Terminal type: automatic
Terminal capacity: 2 x 2.5 mm²
Stripping length: 11 mm

5. OPERATION



6. TECHNICAL CHARACTERISTICS

■ 6.1 Mechanical characteristics

Protection against impacts: IK 04
Protection against solid bodies and/or liquids: IP 41

■ 6.2 Material characteristics

Mechanism casing: PC
Grid: 6.6 PC + Galfan steel
Plates: White ABS + PC (RAL 9003) polyglass appearance
Painted Titanium or Graphite ABS + metal
Cover plate: PC
Ring: ABS
Halogen-free
UV-resistant

Self-extinguishing:
850°C/30 s for insulating components holding live parts in place.
650°C/30 s for other insulating components.

6. TECHNICAL CHARACTERISTICS *(continued)*

■ 6.3 Electrical characteristics

Voltage: 110/230 V~

Current: 16 A

Power: 3680 W max.

Frequency: 50/60 Hz

Standby consumption: 0.1 mA

Technologie Zigbee

Frequency: 2.4 GHz to 2.4835 GHz

Power level: < 100 mW

Range: 200 m of unobstructed space between 2 wired products

10 m between products indoors

■ 6.4 Climate characteristics

Storage temperature: 0°C to +45°C

Usage temperature: +5°C to +45°C

7. CARE

Clean the surface with a cloth.

Do not use acetone, tar-removing cleaning agents or trichloroethylene.

Resistant to the following products:

Hexane (EN 60669-1), methylated spirit, soapy water, diluted ammonia, bleach diluted to 10%, window-cleaning products, pre-impregnated wipes.

Caution: Always test before using special cleaning products.

Do not paint the plate.

8. STANDARDS AND APPROVALS

Compliant with installation and manufacturing standards.

See e-catalogue.

The undersigned, LEGRAND, declares that the radio-electric equipment type (1 991 61/71/81) complies with directive 2014/53/EU.

The full text of the EU declaration of conformity is available on the following website www.legrandoc.com