


## Céliane™ Ring 2-way switch

Cat. No(s): CM0006/1006/2006 - CM0030/1030




### 1. USE

Light control toggle mechanisms with ring-shaped button.  
 Allow ON/OFF lighting control with direct action on the ring.  
 To be combined with a dedicated hubcap and a Materials finishing plate.

### 2. RANGE

Description	Cat. No(s)
Ring two-way switch	CM0006
Ring two-way switch with luminous indicator light	CM1006
Ring two-way switch with indicator light	CM2006
Ring changeover push button	CM0030
Ring changeover push button with luminous indicator light	CM1030

### 3. DIMENSIONS (mm)



A	B	C	D
74	74	36.5	14

### 4. CONNECTION

Type of terminals: automatic  
 Terminal capacity: 2 x 2.5 mm<sup>2</sup>  
 Stripping length: 12 mm  
 LEDs: 2 wires to be wired

### 5. TECHNICAL CHARACTERISTICS

#### ■ 5.1 Mechanical characteristics

Impacts tests: IK 04  
 Protection against solid/bodies and liquids: IP 20

#### ■ 5.2 Material characteristics

Mechanism casing: PC  
 Halogen-free

#### Self-extinguishing:

850°C/30 s for insulating components holding live parts in place.  
 650°C/30 s for other insulating components.

#### ■ 5.3 Electrical characteristics

Voltage: 250 V~  
 Current: 10 AX (CM0006/1006/2006)  
 Max. power for self-ballasted lamps: 100 W  
 Current: 6 A (CM0030/1030)

Luminous indicator light (CM0227): 230 V - 0.15 mA

Indicator light (CM0228): 230 V - 2.4 mA

#### ■ 5.4 Climate characteristics

Storage temperature: -10°C to +70°C  
 Usage temperature: -5°C to +35°C

### 6. STANDARDS AND APPROVALS

Compliant with installation and manufacturing standards.  
 See e. catalogue.