



# Céliane™

## German standard power sockets


Cat. No(s): CM0120 - CM0121 - CM0123



CM0120



CM0121



CM0123


### 1. USE

2 P+E socket outlets, shuttered.

### 2. RANGE

Description	Cat. Nos
2 P+E socket outlet. Lateral earth contact mechanism.	CM0120
2 P+E socket with clip cover plate not supplied on mechanism, with screwed terminals on the front.	CM0121
2 P+E socket with dedicated cover plate supplied on mechanism	CM0123


### 3. DIMENSIONS (mm)



References	A	B	C	D
CM0120	45	45	40	5.5
CM0121	45	45	36.5	5.5
CM0123	45	45	40	8.5

### 4. PRODUCTS WITH BULB

■ Ref. CM0120 / CM0121



### 5. CONNECTION

#### ■ Cat. Nos CM0120

Terminal type: automatic  
Terminal capacity: 2 x 2.5 mm<sup>2</sup>  
Stripping length: 12 mm

#### ■ Cat. Nos CM0121 - CM0123

Terminal type: with screws  
Terminal capacity: 4 mm<sup>2</sup>  
Stripping length: 10 mm  
Screwdriver: Posidrive No 1, Philips No 1, flat-blade 4 mm

### 6. TECHNICAL CHARACTERISTICS

#### ■ 6.1 Mechanical characteristics

Impact tests: IK 04  
Protection against solide bodies and liquids: IP 20  
IP 44 : Ref. CM0120 (with specific cover plate and gang plate)

#### ■ 6.2 Material characteristics

Mechanism casing: PC  
Face plate: PC  
Halogen-free  
Self-extinguishing:  
850°C/30 s for insulating components holding live parts in place.  
650°C/30 s for other insulating components.

#### ■ 6.3 Electrical characteristics

Voltage: 250 V~  
Current: 16 A

#### ■ 6.4 Climate characteristics

Storage temperature: -10°C to +70°C  
Usage temperature: -5°C to +50°C

### 7. ACCESSORIE

Bulb Cat. No 0 676 64 (230 Vac - 2.4 mA)

### 8. STANDARDS AND APPROVALS

Compliant with installation and manufacturing standards.  
See e-catalogue.