



Céliane™ Key card switches

Cat. No(s): CM0010 - CM0012



CM0010



CM0012

1. USE

For energizing a circuit by inserting a key fob or a smart card (access card for a hotel room).

Time delay of approx. 30 seconds after card removal.


Surface or recessed installation in box depth 40 mm minimum.

Multi-station horizontal mounting with 71 mm center distance.

2. GAMME

Description	Cat. Nos
Key card switch Possibility of combining it with the call button Cat. No CM0035	CM0010
Key card switch RFID Works only by detecting the presence of a badge equipped with ISO type 13.56 MHz key card.	CM0012

3. DIMENSIONS (mm)



A	B	C	D
45	45	35.5	15.5

4. CONNECTION

Type of terminals: with screws

Terminal capacity: 2 x 2.5 mm²

Stripping length: 8 mm

Screwdriver: flat 4 mm

Compatible with flexible or rigid cables.

5. TECHNICAL CHARACTERISTICS

■ 5.1 Mechanical characteristics

Impact tests: IK 04

Penetration by solid bodies and liquids: IP 20

■ 5.2 Material characteristics

Mechanism casing: PC

Hood: PC

Halogen-free

Self-extinguishing:

850°C/30 s for insulating components holding live parts in place.

650°C/30 s for other insulating components.

■ 5.3 Electrical characteristics

Voltage: 230 V~

Current: 0.25 A

Power: 12 W

Frequency: 50/60 Hz

■ 5.4 Climate characteristics

Usage temperature: -5°C to +35°C

Storage temperature: -10°C to +70°C

6. CARE

Surface cleaning with a cloth.

Regular dusting of the piston head (Cat. No. CM0010) using a small brush.

7. STANDARDS AND APPROVALS

Compliant with installation and manufacturing standards.

See e.catalogue.