



## Surface-mounted equipment Reversible Transformeur

Cat. No(s): **0 860 20L**  
**0 861 14L/20L**



### 1. USE

Lighting control mechanisms.



Lighting control mechanisms with possible functions:

\_ Double two-way or double push button.

\_ One two-way or one push button in right or left position.



Supplied in change-over push-button mode with 2 half-fingers monted.

### 2. RANGE

		References
Configurable		0 861 14L 0 861 20L
		0 860 20L

### 3. OVERALL DIMENSIONS (mm)

#### ■ Surface-mounting



### 3. OVERALL DIMENSIONS (mm) (continued)

	A	B	C
<b>Configurable</b>	53.5	54.8	29.5
<b>Surface-mounting complete</b>	72	72	31.4

### 4. CONNECTION

Type of terminals: automatic

Terminal capacity: 1.5 mm<sup>2</sup> - 2.5 mm<sup>2</sup> (1 or 2 conductors)

Stripping length: 12 mm

### 5. TECHNICAL CHARACTERISTICS

#### ■ 5.1 Protection index

Protection against solid bodies and liquids: IP 31D

Protection against impact: IK 04

#### ■ 5.2 Material characteristics

Frame, support : PS

Rocker: ABS + PC

Mechanism: PC

UV-resistant

Halogen-free

Self-extinguishing:

850°C/30 s for insulating components holding live parts in place.

650°C/30 s for other insulating components.

#### ■ 5.3 Electrical characteristics

Voltage: 250 V~

Frequency: 50 Hz

Current: Push button version 10 A


Two-way version 10 AX

Maximum power on lamps with integrated ballast  
 (LED lamps and compact fluorescent): 100 W

#### ■ 5.4 Climate characteristics

Usage temperature: - 10° to + 40° C

Storage temperature: - 25° C to + 60° C



## 6. CLEANING

Surface cleaning with a cloth.

Do not use: acetone, tar remover, trichloroethylene.

Maintenance with the following products: Hexane (EN 60669-1), Methylated spirit, Soapy water, Diluted ammonia, Bleach diluted to 10%, Window-cleaning products, Pre-saturated wipes.

**Caution:** A preliminary test should be carried out if other specific cleaning products are to be used.

## 7. STANDARDS AND APPROVALS

Compliance with standards of installation and manufacturing.  
Refer to e. catalogue.