


Céliane™

16 AX 2-pole switch

Cat. No(s): CM0020




1. USE

Lighting control mechanism.
 Horizontal and vertical multi-gang mounting.
 To be equipped with support, face plate and finishing plate.

2. RANGE

Description	Cat. No
2-pole switch For simultaneous breaking of phase and neutral. Can be illuminated (with bulb Cat. No. CM0224) or signalling (with bulb Cat. No. CM0225); takes cover plates (Cat. No. CB1020 white, Cat. No. CI1020, Cat. No. CN1020 black, Cat. No. CT1020 titanium).	CM0020

3. DIMENSIONS (mm)



A	B	C	D
45	45	31	7

4. CONNECTION

Type of terminals: with screws
 Terminal capacity: 2 x 2.5 mm²
 Stripping length: 9 mm

5. TECHNICAL CHARACTERISTICS

■ 5.1 Mechanical characteristics

Impact test: IK 04
 Penetration by solid bodies and liquids: IP 20

■ 5.2 Material characteristics

Mechanism casing: PC
 Halogen-free

Self-extinguishing:

85°C/30 s for insulating components holding live parts in place.
 65°C/30 s for other insulating components.

■ 5.3 Electrical characteristics

Voltage: 250 V~
 Current: 16 AX
 Max. power for self-ballasted lamps: 200 W

■ 5.4 Climate characteristics

Storage temperature: - 10°C to + 70°C
 Usage temperature: - 5°C to + 50°C

6. ACCESSORIES

Wiring indicators :

Indicator lighting	Locator lighting
CM0224 (230 V - 0,15 mA)	CM0225 (230 V - 3 mA)

7. STANDARDS AND APPROVALS

Compliant with installation and manufacturing standards.
 See e-catalogue.