


Surface-mounted equipment Single reversible transformer



Cat. No(s): **0 860 01L**
0 861 01L



1. USE


Lighting control mechanisms.
 Lighting control mechanisms with feasible functions:
 _ Simple back and forth.
 _ Simple push button.
 Delivered in reversing push-button mode with 1 single finger mounted.

2. RANGE


		References
Configurable		0 861 01L
Surface-mounting complete		0 861 01L

3. OVERALL DIMENSIONS (mm)

■ Configurable



■ Surface-mounting



3. OVERALL DIMENSIONS (mm) (continued)


	A	B	C
Configurable	53.5	54.7	29.5
Surface-mounting complete	72	72	31.4

4. CONNECTION

Type of terminals: automatic
 Terminal capacity: 1.5 mm² - 2.5 mm² (1 or 2 conductors)
 Stripping length: 12 mm

5. TECHNICAL CHARACTERISTICS

- **5.1 Protection index**
 Protection against solid bodies and liquids: IP 31D
 Protection against impact: IK 04
- **5.2 Material characteristics**
 Frame, support, rocker: ABS
 Mechanism: PC
 UV-resistant
 Halogen-free
 Self-extinguishing:
 850°C/30 s for insulating components holding live parts in place.
 650°C/30 s for other insulating components.
- **5.3 Electrical characteristics**
 Voltage: 250 V~
 Frequency: 50 Hz
 Current: Push button version 10 A
 Two-way version 10 AX
 Maximum power on lamps with integrated ballast
 (LED lamps and compact fluorescent): 100 W
- **5.4 Climate characteristics**
 Usage temperature: - 10° to + 40° C
 Storage temperature: - 25° C to + 60° C



6. CLEANING

Surface cleaning with a cloth.

Do not use: acetone, tar remover, trichloroethylene.

Maintenance with the following products: Hexane (EN 60669-1), Methylated spirit, Soapy water, Diluted ammonia, Bleach diluted to 10%, Window-cleaning products, Pre-saturated wipes.

Caution: A preliminary test should be carried out if other specific cleaning products are to be used.

7. STANDARDS AND APPROVALS

Compliance with standards of installation and manufacturing.
Refer to e. catalogue.