



Céliane™ Cable outlets

Cat. No(s): CM0181- CM0183



CM0181



CM0183


1. USAGE

Cable outlets with cable clamps.
 The mechanisms are mounted recessed or surface-mounted, in multiple positions horizontally or vertically.

2. RANGE

Description	Cat. No.
Cable outlet supplied with cable clamps. For cables Ø max 12.5 mm, Ø min 4 mm. Authorized cables H05 VVF or H07 RNF. 2 modules	CM0181
Cable outlet with terminal blocks delivered with cable clamps For cables Ø max 12.5 mm, Ø min 4 mm. 2 modules	CM0183

3. DIMENSIONS (mm)



Cat. Nos	A	B	C	D
CM0181	45	45	30.5	8
CM0183	45	45	38	8

4. CONNECTION

Cat. No CM0183

Type of terminals: automatic

Stripping length: 12 mm

Cable cross section: front panel: 4 x 1.5 mm²
 rear side: 4 x (2 x 1.5 mm²)

5. TECHNICAL CHARACTERISTICS

■ 5.1 Mechanical characteristics

Protection against solid bodies and liquids: IP 20

Protection against impact: IK 04

■ 5.2 Material characteristics

Mechanism casing: PC

Halogen-free

Self-extinguishing:

850°C/30 s for insulating components holding live parts in place.

650°C/30 s for other insulating components.

■ 5.3 Electrical characteristics

Cat. No CM0183

Voltage: 250 V~

Current: 10 A

■ 5.4 Climate characteristics

Storage temperature: -10°C to +70°C

Usage temperature: -5°C to +35°C

6. CARE

Surface cleaning with a cloth.

Do not use: acetone, tar remover, trichloroethylene.

Caution: Always test before using special cleaning products.

7. STANDARDS AND APPROVALS

Compliant with installation and manufacturing standards.

See e-catalogue.