



## Surface-mounted equipment 2-way ventilation control

Cat. No(s): **0 860 16L**  
**0 861 16L**



### 1. USE


Control mechanisms for controlled mechanical ventilation

### 2. RANGE


		References
Configurable		0 861 16L
Surface-mounting complete		0 861 16L

### 3. OVERALL DIMENSIONS (mm)

#### ■ Configurable



#### ■ Surface-mounting



### 3. OVERALL DIMENSIONS (mm) (continued)

	A	B	C
Configurable	53.5	54.7	29.5
Surface-mounting complete	72	72	31.4

### 4. CONNECTION

Type of terminals: automatic  
 Terminal capacity: 1.5 mm<sup>2</sup> - 2.5 mm<sup>2</sup> (1 or 2 conductors)  
 Stripping length: 12 mm

### 5. TECHNICAL CHARACTERISTICS

#### ■ 5.1 Protection index

Protection against solid bodies and liquids: IP 31D  
 Protection against impact: IK 04

#### ■ 5.2 Material characteristics

Frame, support, rocker: ABS  
 Mechanism: PC


UV-resistant  
 Halogen-free

#### Self-extinguishing:

850°C/30 s for insulating components holding live parts in place.  
 650°C/30 s for other insulating components.

#### ■ 5.3 Electrical characteristics

Voltage: 250 V~  
 Frequency: 50 Hz  
 Current: 10 AX  
 Maximum power on lamps with integrated ballast (LED lamps and compact fluorescent): 100 W



#### ■ 5.4 Climate characteristics

Usage temperature: - 10° to + 40° C  
 Storage temperature: - 25° C to + 60° C

### 6. CLEANING

Surface cleaning with a cloth.

Do not use: acetone, tar remover, trichloroethylene.

Maintenance with the following products: Hexane (EN 60669-1), Methylated spirit, Soapy water, Diluted ammonia, Bleach diluted to 10%, Window-cleaning products, Pre-saturated wipes.

**Caution:** A preliminary test should be carried out if other specific cleaning products are to be used.

### 7. STANDARDS AND APPROVALS

Compliance with standards of installation and manufacturing.  
Refer to e. catalogue.