


Surface-mounted equipment Light indicators


Cat. No(s): 0 899 03L/04L/05L




1. USE

Light indicator for surface-mounted equipment.
 Illuminated and signalling indicators.
 Connection by direct or independent mounting with lamp free maintenance (LED).

2. RANGE

	References: Designations
	0 899 03L : 12V-24V-48V white 0 899 04L : 230V white - light function 0 899 05L : 230V white - indicator function

3. OVERALL DIMENSIONS (mm)



A	B	C	D
13	19.5	145.5	8.5

4. CONNECTION

2 wires supplied to wire to the mechanisms.

5. TECHNICAL CHARACTERISTICS

■ 5.1 Protection index

Protection against solid bodies and liquids: IP 31D (mounted)
 Protection against impact: IK 04 (alone)

■ 5.2 Material characteristics

UV-resistant
 Halogen-free
 Self-extinguishing:
 850°C/30 s for insulating components holding live parts in place.
 650°C/30 s for other insulating components.

■ 5.3 Electrical characteristics

References	Voltage	Consumption	Function
0 899 03L	12 V~ / 12 V=	0.6 mA / 1.06 mA	White
	24 V~ / 24 V=	1.3 mA / 2.41 mA	
	48 V~ / 48 V=	2.8 mA / 5.15 mA	
0 899 04L	230 V~	0.126 mA	Light function White
0 899 05L	230 V~	1.89 mA	Indicator White

■ 5.4 Climate characteristics

Usage temperature: - 10° to + 40° C
 Storage temperature: - 25° C to + 60° C

6. CLEANING

Surface cleaning with a cloth.
 Do not use: acetone, tar remover, trichloroethylene.
 Maintenance with the following products: Hexane (EN 60669-1),
 Methylated spirit, Soapy water, Diluted ammonia, Bleach diluted
 to 10%, Window-cleaning products, Pre-saturated wipes.

Caution: A preliminary test should be carried out if other specific cleaning products are to be used.

7. STANDARDS AND APPROVALS

Compliance with standards of installation and manufacturing.
 Refer to e. catalogue.