


## Urbano™ VMC control

Cat. No(s): UB9410GR/WH



### 1. USE


Control mechanisms for controlled mechanical ventilation.  
 The mechanisms are supplied with rocker, supports and plates.  
 Equipped with single-post plates.  
 Flush mounting mechanisms  
 Fixing with claws and/or screws.

### 2. RANGE

#### VMC Control 10 AX - 250 V~ - with claws

Description	White	Grey
2 position vmc switch	UB9410WH	UB9410GR

### 3. OVERALL DIMENSIONS (mm)



References	A	B	C	D
UB9410GR/WH	80	80	35.8	21

### 4. CONNECTION

Type of terminals: screw  
 Terminal capacity: 1.5 mm<sup>2</sup> - 2.5 mm<sup>2</sup> (1 or 2 conductors)  
 Stripping length: 9 mm  
 Flexible or rigid cables compatible.

### 5. TECHNICAL CHARACTERISTICS

#### ■ 5.1 Protection index

Protection against solid bodies and liquids: IP20  
 Protection against impacts: IK 04

#### ■ 5.2 Material characteristics

Front plate, rocker: ABS  
 Mechanism, support : PC  
 Claws: steel


UV-resistant  
 Halogen-free

#### Self-extinguishing:

850°C/30 s for insulating components holding live parts in place.  
 650°C/30 s for other insulating components.

#### ■ 5.3 Electrical characteristics

Voltage: 250 V~  
 Current: 10 AX  
 Frequency: 50/60 Hz  
 Maximum power on lamps with integrated ballast  
 (LED lamps and compact fluorescent): 100 W



#### ■ 5.4 Climate characteristics

Storage temperature: - 10° C to + 70° C  
 Use temperature: - 5° C to + 40° C

### 6. CLEANING

Surface cleaning with a cloth.

Do not use: acetone, tar remover, trichloroethylene.

Maintenance with the following products: Hexane, Methylated spirit, Soapy water, Diluted ammonia, Bleach diluted to 10%, Window-cleaning products, Pre-saturated wipes.

**Caution:** A preliminary test should be carried out if other specific cleaning products are to be used.

### 7. STANDARDS AND APPROVALS

Compliance with standards of installation and manufacturing.  
 Refer to e.catalogue.