


# SEANO™ Interlocked control for opening

Cat. No(s): 7 650 47/48



7 650 47/48

### 1. USE


Mechanically and electrically interlocked control mechanisms for roller shutters, blinds and awnings.  
 Flush-mounting or surface-mounting.

Screw and/or claw fixing.


### 2. RANGE

Description	Mechanism Only
ROLLER BLIND PUSH BUTTON	7 650 47
ROLLER BLIND SWITCH	7 650 48

### 3. DISMANTLING



### 4. DIMENSIONS (mm)




References	A	B	C	D
7 65X 08	72,9	72,9	38,5	11,2


### 5. CONNECTION

Flexible cables only  
 TYPE OF TERMINALS:  
 Auto terminal  
 TERMINAL CAPACITY:  
 2 x 2.5mm<sup>2</sup>/terminal  
 STRIPPING LENGTH:  
 13mm

#### 5.1 Switch wiring (7 650 47)



#### 5.2 Push Switch wiring (7 650 48)



## 6. TECHNICAL CHARACTERISTICS

### ■ 6.1 Mechanical characteristics

IProtection against solid bodies and liquids: IP20  
Protection against impact: IK04

### ■ 6.2 Material characteristics

Cover: ABS  
Base: Polycarbonate  
Halogen-free  
UV-resistant  
Self-extinguishing:  
• 850°C/30 s for insulating components holding live parts in place.  
• 650°C/30 s for other insulating components.

### ■ 6.3 Electrical characteristics


Voltage: 250 V~  
Current: 6 AX for 7 650 47  
6 A for 7 650 48  
Frequency: 50/60 Hz

### ■ 6.4 Climate characteristics

Operating temperature: 0°C to +40°C  
Storage temperature: -10°C to +70°C


### ■ 6.5 Support

Material of support: -Metal  
Angular adjusting:



### ■ 6.6 Fixing with claws

Number of turns to open the claws:  
- 58 mm > 2,1 turns  
- 65 mm > 2,75 turns



Performance of double teeth claws: extraction resistance

## 7. MAINTENANCE

Clean the surface with a cloth.  
Do not use: Acetone, tar remover, trichloroethylene.  
Resistance to cleaning products:  
Hexane (EN 60669-1), Methylated spirit, Soapy water, Diluted ammonia,  
Bleach diluted to 10%, Window-cleaning products.

**Caution:** Always test before using other special cleaning products.

## 8. STANDARDS AND APPROVALS

Compliant with installation and manufacturing standards.  
See e. catalogue.