



## Arteor™ Advance

### Cable and cord outlets, cable junction


Cat. no(s): AC350MW - AC351MW  
AC352MW/CH/DB/RS - AC353MW



AC351MW



AC350MW



AC352MW/CH/DB/RS


#### 1. USE

Cable and cord outlets for cables of different diameters.  
Cable junction: AC350MW

#### 2. RANGE

| Designation                  | Matt White | Chapagne | Dark Bronze | Rose    |
|------------------------------|------------|----------|-------------|---------|
| Cord outlet 8 mm<br>1 module | AC351MW    | -        | -           | -       |
| Cable outlet<br>2 modules    | AC353MW    | -        | -           | -       |
| Cable junction<br>2 modules  | AC350MW    | -        | -           | -       |
| Cable outlet                 | AC352MW    | AC352CH  | AC352DB     | AC352RS |

#### 3. DIMENSIONS (mm)



| Cat. No(s)       | A  | B    | C    | D     |
|------------------|----|------|------|-------|
| AC351MW          | 45 | 22.5 | 24.5 | 8.5   |
| AC353MW          | 45 | 45   | 38.5 | 19.5  |
| AC350MW          | 45 | 45   | 32.5 | 12.5  |
| AC352MW/CH/DB/RS | 92 | 92   | 44   | 25.25 |

#### 4. CONNECTION

##### Max. diameters of cable to be used:

Cat. No AC351MW: 8 mm  
Cat. No AC353MW: 12.5 mm

##### Cat. No AC350MW:

Type of connection with screws  
Stripping length: 7mm  
Terminal capacity: 6 x 2.5 mm<sup>2</sup>  
Type of screwdriver: flat blade 4 mm

##### Cat. No AC352MW/CH/DB/RS:

Type of connection: with screws  
Stripping length: 14 mm  
Capacity: 2 x 6 mm<sup>2</sup> to 1 x 10 mm<sup>2</sup>  
Type of screwdriver: flat blade 4 mm

#### 5. TECHNICAL CHARACTERISTICS

##### ■ 5.1 Mechanical characteristics

Impact tests: IK 04  
Protection against solid bodies and liquids: IP20

##### ■ 5.2 Material characteristics

Cover: PC  
Base: PC  
Halogen-free  
UV-resistant  
Self-extinguishing:  
850°C/30 s for components holding live parts in place  
650°C/30 s for other insulating components

##### ■ 5.3 Electrical characteristics

Voltage: 250 V~  
Current: Cat. No. AC350MW = 20 A  
Cat. No. AC352MW/CH/DB/RS = 45 A

##### ■ 5.4 Climate characteristics

Storage temperature: - 10°C to + 70°C  
Operating temperature: - 5°C to + 35°C

#### 6. CLEANING

Clean the surface with a cloth.  
Do not use acetone, tar-removing cleaning agents or trichloroethylene.  
Resistant to the following products: Hexane, methylated spirit, soapy water, diluted ammonia, bleach diluted to 10%, window-cleaning products, pre-impregnated wipes.

**Caution:** Always test before using special cleaning products.

7. STANDARDS AND APPROVALS

Compliant with installation and manufacturing standards.  
See e.catalogue.