


# Céliane™

## Dimmer for 1-10 V ballast, with neutral

Cat. No(s): CM0061



### 1. USAGE

Permet la commande et la variation de tubes fluo à ballast électronique 1-10 V.


For installation in a flush-mounting box, min. 40 mm deep.

Fixing with screws.

### 2. GAMME

Description	Reference
Dimmer for 1-10 V ballasts with neutral. Includes level memory function. Mechanism to be combined with support, cover and finishing plate.	CM0061

### 3. DIMENSIONS (mm)



A	B	C	D
45	45	41	7


### 4. CONNECTION

Type of terminals: with screws

Terminal capacity: 2 x 2,5 mm<sup>2</sup>

Stripping length: 8 mm

### 5. OPERATION



### 6. TECHNICAL CHARACTERISTICS

#### ■ 6.1 Mechanical characteristics

Protection against impacts: IK 02

Protection against solid bodies and liquids: IP 20

#### ■ 6.2 Material characteristics

Mechanism casing: PC

Halogen-free

Self-extinguishing:

850°C/30 s for insulating components holding live parts in place.

650°C/30 s for other insulating components.

#### ■ 6.3 Electrical characteristics

Voltage: 100-240 V~

Power: Max. 600 W

Current: Max. 40 mA

Frequency: 50/60 Hz

#### ■ 6.5 Climate characteristics

Operating temperature: +5°C to +35°C

Storage temperature: 0°C to +45°C

### 7. CLEANING

Surface cleaning with a cloth.

### 8. STANDARDS AND APPROVALS

Compliant with installation and manufacturing standards.

See e. catalogue.