



## Urbano™ Push-buttons 6 A

Cat. No(s): UB2310GR/WH - UB2311GR/WH - UB2312GR/WH



### 1. USE


Lighting control mechanisms.  
 Supplied with rockers, support frames and plate.  
 Equipped with one-gang plate.  
 Flush or surface mounting.  
 Fixing with screws or/and claws.

### 2. RANGE

#### PUSH-BUTTON 6 A - 250 V~ - with claws

Description	White	Grey
Push-button	UB2310WH	UB2310GR
Lighting push-button	UB2311WH	UB2311GR
Bell push-button	UB2312WH	UB2312GR

### 3. OVERALL DIMENSIONS (mm)



References	A	B	C	D
UB2310GR/WH - UB2311GR/WH - UB2312GR/WH	80	80	35.8	21

### 4. CONNECTION

Type of terminals: screw  
 Terminal capacity: 1.5 mm<sup>2</sup> - 2.5 mm<sup>2</sup> (1 or 2 conductors)  
 Stripping length: 9 mm  
 Flexible or rigid cables compatible.

### 5. TECHNICAL CHARACTERISTICS

#### ■ 5.1 Protection index

Protection against solid bodies and liquids: IP20  
 Protection against impacts: IK 04

#### ■ 5.2 Material characteristics

Front plate, rocker: ABS  
 Mechanism, support : PC  
 Claws: steel

UV-resistant  
 Halogen-free

#### Self-extinguishing:

850°C/30 s for insulating components holding live parts in place.  
 650°C/30 s for other insulating components.

#### ■ 5.3 Electrical characteristics

Voltage: 250 V~  
 Current: 6 A  
 Frequency: 50/60 Hz

#### ■ 5.4 Climate characteristics

Storage temperature: - 10° C to + 70° C  
 Use temperature: - 5° C to + 35° C

### 6. CLEANING

Surface cleaning with a cloth.

Do not use: acetone, tar remover, trichloroethylene.

Maintenance with the following products: Hexane (EN 60669-1),  
 Methylated spirit, Soapy water, Diluted ammonia, Bleach diluted to 10%,  
 Window-cleaning products, Pre-saturated wipes.

**Caution:** A preliminary test should be carried out if other specific cleaning products are to be used.

### 7. STANDARDS AND APPROVALS

Compliance with standards of installation and manufacturing.  
 Refer to e.catalogue.