



Arteor™ Advance Fan controllers

Cat. No(s): AC662MW/MB/MT - AA667MW/MB/MT - AC668MW/MB/MT



AC662MW/MB/MT
AA667MW/MB/MT



AC668MW/MB/MT


1. USE

Rotary speed controller for fan.

2. RANGE

Description	Matt White	Matt Black	Matt Titanium
2 modules, Fan controller for energy saving	AC662MW	AC662MB	AC662MT
2 modules, Fan controller for energy saving	AA667MW	AA667MB	AA667MT
2 modules, AC speed fan controller for energy saving, 4 steps	AC668MW	AC668MB	AC668MT

3. DIMENSIONS (mm)



Cat. Nos	A	B	C	D
AC662MW/MB/MT AA667MW/MB/MT	45	45	58.5	25.5
AC668MW/MB/MT	45	45	42	9

4. CONNECTION

Type of terminal: with screws
Capacity: 2 x 1.5 mm² or 1 x 2.5 mm²
Screwdriver: flat-blade 3.5 mm

5. TECHNICAL CHARACTERISTICS

■ 5.1 Mechanical characteristics

Impact test: IK 04
Protection against solid bodies and liquids IP 20

■ 5.2 Material characteristics

Rocker: PC
Mechanism: PC
Self-extinguishing:
850°C/30 s for insulating parts holding live parts in place.
650°C/30 s for other parts made of insulating materials.

■ 5.3 Electrical characteristics

Cat. Nos	Voltage	Power
AC662MW/MB/MT	240 V	100 W
AC668MW/MB/MT	250 V	2300 W
AA667MW/MB/MT	240 V	70 W

Frequency: 50/60 Hz

■ 5.3 Climate characteristics

Usage temperature: 0°C to +35°C
Storage temperature: -10°C to +70°C

6. CLEANING

Clean the surface with a cloth.
Do not use acetone, tar-removing cleaning agents or trichloroethylene.
Resistant to the following products: Hexane, methylated spirit, soapy water, diluted ammonia, bleach diluted to 10%, window-cleaning products, pre-impregnated wipes.

Caution: Always test before using special cleaning products.

6. STANDARDS AND APPROVALS

Conforme to IEC 60669-1 Standard.
Compliant with installation and manufacturing standards.
See e.catalogue.