


Céliane™

Contactless switch for door, gate release, electromagnetic suction pad

Cat. No(s): CM0004



1. USE

Opens the door by simply passing a hand in front of the switch.
 Detection distance adjustable from 10 cm (default) to 30 cm.

Available modes:


- Maintained/pulse mode (default mode)
- NC/NO mode (default mode)

For installation in any type of box.

2. RANGE

Description	Cat. No.
Contactless switch for door, gate release, electromagnetic suction pad. With illuminated indicator, active by default (can be deactivated). To be equipped with support frame, rocker plate and finishing plate.	CM0003

3. DIMENSIONS (mm)



A	B	C	D
45	45	25	6.5

4. CONNECTION

Terminal type: with screws
 Terminal capacity: 2 x 2.5 mm²
 Stripping length: 8 mm

5. TECHNICAL CHARACTERISTICS

■ 5.1 Mechanical characteristics

Impact tests: IK 04
 Protection against solid bodies and liquids: IP 40

■ 5.2 Material characteristics

Mechanism casing: PC

Halogen-free

Self-extinguishing:

850°C/30 s for insulating components holding live parts in place.
 650°C/30 s for other insulating components.

■ 5.3 Electrical characteristics

Supply voltage: 12 - 24 - 48 VDC

Power: 24 VA

Frequency: 50/60 Hz

■ 5.4 Climate characteristics

Storage temperature: -10°C to +70°C

Usage temperature: -5°C to +35°C

6. CARE

Surface cleaning with a cloth.

Do not use: acetone, tar remover, trichloroethylene.

Caution: Always test before using other special cleaning products.

7. STANDARDS AND APPROVALS

Compliant with installation and manufacturing standards.
 See e.catalogue.