



Obria™
Cable Outlet

 Cat. No(s): MEC35058/59XX MY
 "XX" = Color / finishes: WH SL CH BL RG
 "MY" = Malaysia


MEC35058XX MY



MEC35059XX

1. USE

Device to enable the connection of free-standing electrical appliances from the fixed wiring of the main installation.
 (Supplied with M3.5 screws for Flush mounting or surface mounting BS boxes.)

2. RANGE

Designation	Cat. No.
20A CABLE OUTLET	MEC35058XX MY
45A CABLE OUTLET	MEC35059XX

Colours

-Matt colors finishes

WH: Matt White

SL: Dark silver

CH: Champagne

BL: Matt Black

RG: Rose gold

3. DIMENSIONS (mm)(continued)

References	A	B	C	D
MEC35058XX MY	87.4	86	39	12
MEC35059XX	86	86	42.9	25.4

4. CONNECTION

Types of terminals: with screws

Terminal capacity of MEC35058XX: 3 × 1 mm²

3 × 1.5 mm²

2 × 2.5 mm²

1 × 4 mm²

Recommended stripping length for MEC35058XX: 12 mm

Terminal capacity of MEC35059XX: 2 × 6 mm²

1 × 10 mm²

Recommended stripping length for MEC35059XX: 17 mm

Recommended screwdriver size: <4 mm flat blade

5. TECHNICAL CHARACTERISTICS
5.1 Material characteristics

Plate: PC

Frame: Steel

Base: PC

Self-extinguishing:

+ 850° C / 30 s for insulating parts holding live parts in place

+ 650° C / 30 s for other parts made of insulating materials

5.2 Electrical characteristics

MEC35058XX:

Voltage: 250V~ Current: 20A

MEC35059XX:

Voltage: 250V~ Current: 45A

5.3 Climatic characteristics

Storage temperatures: -10°C to +70°C

Operating temperatures: -5°C to +35°C

5.4 Mechanical characteristics

Impact test: IK04

Protection against solids & liquids: IP20

6. CLEANING

Surface cleaning with a soft, slightly damp cloth.

Do not use: acetone, tar remover, trichloroethylene

7. CONFORMITY - APPROVALS

Conform to BS 5733.