



Arteor™ Advance with Netatmo Smart Home/Away wireless control

Cat. No(s): AC5704MW/MB/MT
AA5704MW/MB/MT



AC5704MW/MB/MT



AC5704MW/MB/MT


1. USE

Used to control leaving home/coming home scenes involving lights, curtains/roller shutters, smart socket outlets.
Requires the prior installation of a smart Gateway "with Netatmo".
Can be installed in a box 35 mm deep minimum.
To be equipped with a frame and plate.

2. RANGE


Designation	Finishes		
	Matt White	Matt Black	Matt Titanium
Smart Home/Away wireless control	AC5704MW	AC5704MB	AC5704MT
	AA5704MW	AA5704MB	AA5704MT

3. DIMENSIONS (mm)



Cat. Nos	A	B	C	D
AC5704MW/MB/MT	45	22.5	44	9
AA5704MW/MB/MT	60	22.5	44	9

4. OPERATION



5. TECHNICAL CHARACTERISTICS

5.1 Mechanical characteristics

Protection against impacts: IK 04
Protection against solid bodies and/or liquids: IP 20

5.2 Material characteristics

Mechanism casing: PC
Rocker: PC or ABS

Halogen-free

UV-resistant

Self-extinguishing: 650° C/30 s

5.3 Electrical characteristics

Powered by a CR2042 - 3 V lithium battery (supplied)
Battery life: 8 years for 10 activations a day

ZigBee radio technology:

Frequency bands: 2.4 GHz to 2.4835 GHz
Power level: < 100 mW
Range: 200 m of unobstructed space

5.4 Climate characteristics

Storage temperature: 0°C to +45°C
Usage temperature: +5°C to +35°C

6. CLEANING

Clean the surface with a cloth.

Do not use acetone, tar-removing cleaning agents or trichloroethylene.

Resistant to the following products:

Hexane, methylated spirit, soapy water, diluted ammonia, bleach diluted to 10%, window-cleaning products, pre-impregnated wipes.

Resistant to hospital grade cleaning products:

Anios, surfanios, bactilysine, diluted hydrogen peroxide (35%).

Caution: Always test before using special cleaning products.



Take care to recycle the battery appropriately.

7. STANDARDS AND APPROVALS

The undersigned, LEGRAND, declares that the radio-electric equipment type smart product "with Netatmo" complies with directive 2014/53/EU.