



## Arteor™ Advance 10 AX Lighting controls

Cat. No(s): AA21105MW/MB/MT - AA22104MW/MB/MT - AC21104MW/MB/MT  
AC21106MW/MB/MT - AC22104MW/MB/MT - AC22105MW/MB/MT




### 1. USE

Lighting controls mechanisms.  
Mechanisms supplied with cover.  
To be equipped with support frame and plate. Flush-mounting or surface-mounting.

### 2. RANGE

Designation	Finishes		
	Matt White	Matt Black	Matt Titanium
1 module 1-way single pole switch with locator	AA21105MW	AA21105MB	AA21105MT
1 module 2-way single pole switch with indicator or locator	AA22104MW	AA22104MB	AA22104MT
1 module 1-way single pole switch	AC21104MW	AC21104MB	AC21104MT
1 module 1-way single pole switch with indicator	AC21106MW	AC21106MB	AC21106MT
1 module 2-way single pole switch with indicator or locator	AC22104MW	AC22104MB	AC22104MT
1 module 2-way single pole switch	AC22105MW	AC22105MB	AC22105MT

3. DIMENSIONS (mm)



Cat. Nos	A	B	C
AA21105MW/MB/MT AA22104MW/MB/MT	61.8	22.5	40.8
AC21104MW/MB/MT AC21106MW/MB/MT AC22104MW/MB/MT AC22106MW/MB/MT	45.05	22.5	38.6

4. CONNECTION

Type of terminals: with screws  
Terminal capacity: 2 x 1.5 mm<sup>2</sup> or 1 x 1.4 mm<sup>2</sup>  
Stripping length: 10 mm

5. TECHNICAL CHARACTERISTICS

■ 5.1 Mechanical characteristics


Impact test: IK 04  
Protection against solid bodies and liquids: IP 40 (mounted)  
IP 20 (alone)

■ 5.2 Material characteristics

Rocker: PC  
Mechanism: PC  
Self-extinguishing:  
850°C/30 s for insulating parts holding live parts in place.  
650°C/30 s for other parts made of insulating materials.

■ 5.3 Electrical characteristics

Voltage: 250 Vac  
Current: 10 AX  
Maximum power on lamps with integrated ballast  
(LED lamps and compact fluorescent): 100 W



■ 5.4 Climate characteristics

Storage temperature: - 10° c to + 70° C  
Usage temperature: - 5° C to + 35° C

6. CLEANING

Surface cleaning with a cloth.  
Do not use: acetone, tar remover, trichloroethylene.  
Resistance to the following agents: Hexane,  
Methylated spirits, Soapy water, diluted ammonia, diluted pure bleach  
10%, Glass cleaning substance, Pre-impregnated wipes.

**Caution:** Always test before using other special cleaning products.

7. STANDARDS AND APPROVALS

Compliance with installation and manufacturing standards.  
Refer to e-catalogue.