



Arteor™ Advance with Netatmo - British Standard Smart color switch wireless control

Cat. No(s): AC5205MW/MB/MT
 AA5205MW/MB/MT



AC5205MW/MB/MT



AA5205MW/MB/MT





1. USE

Wireless switch to control multicolor smart lighting.
 Requires the prior installation of a smart Gateway for connected installation or a Control modul "with Netatmo".
 Controls any kind of Zigbee 3.0 certified bulbs and lighting (such as Ledvance, Smart + Zigbee, Philips HUE and many others).
 Can be used as a two-way switch or to control a lighting group.
 • Fixes directly on the wall or screws onto a fush-mounting box.
 Multi-gang versions can be combined with other wiring accessories.
 • Fits on a piece of furniture (movable).
 Can control up to 20 connected zigbee 3.0 lights.

2. RANGE

Description	Matt White	Matt Black	Matt Titanium
Smart color switch wireless control with battery. Supplied with a secable support frame and a rocker. 3 ambiances (I - II - III) to select in Home + Control App. Equipped with an LED indicator (configuration) and a RESET button (hidden) used to return to factory settings. Repositionable self-adhesive fixings (supplied). To be equipped with finishing plate.	AC5205MW AA5205MW 2-gang	AC5205MB AA5205MB 2-gang	AC5205MT AA5205MT 2-gang


3. DIMENSIONS (mm)



A	B	B'	C
86	123	86	11.8

A	B	B'	C
86	123	86	12.1

4. OPERATION



5. TECHNICAL CHARACTERISTICS

■ 5.1 Mechanical characteristics

Protection against impacts: IK 02

Protection against solid bodies and/or liquids: IP 20

■ 5.2 Material characteristics

Rocker: PC

Mechanism casing with grid: Fibreglass-reinforced (20%) PC

Halogen-free

UV-resistant

Self-extinguishing: 650°C/30 s

■ 5.3 Electrical characteristics

Powered by a CR2032 - 3 V lithium battery (supplied)

Battery life: 8 years for 10 activations a day

ZigBee radio technology

frequency: 2.4 GHz to 2.4835 GHz

Power level: < 100 mW

■ 5.4 Climate characteristics

Storage temperature: 0° C to + 45° C

Usage temperature: +5° C to + 35° C

6. CARE

Clean the surface with a cloth.

Do not use acetone, tar-removing cleaning agents or trichloroethylene.

Resistant to the following products:

Hexane, methylated spirit, soapy water, diluted ammonia, bleach diluted to 10%, window-cleaning products, pre-impregnated wipes.

Caution: Always test before using special cleaning products.



Take care to recycle the battery appropriately.

7. STANDARDS AND APPROVALS

Compliant with installation and manufacturing standards.

The undersigned, LEGRAND, declares that the radio-electric equipment type (AC5205MW/MB/MT, AA5205MW/MB/MT) complies with directive 2014/53/EU.

The full text of the EU declaration of conformity is available on the following website: www.legrand.com/ecatalogue