



Arteor™ Advance BS 13A socket outlets


Cat. No(s): AA3201MW/MB/MT/CH/DB/RS - AA3202MW/MB/MT/CH/DB/RS
AA3203MW/MB/MT/CH/DB/RS - AA3207MW/MB/MT/CH/DB/RS
AA3208MW/MB/MT/CH/DB/RS - AA3209MW/MB/MT/CH/DB/RS
AA3140MW/MB/MT/CH/DB/RS - AA3141MW/MB/MT/CH/DB/RS




AA3201MW/MB/MT/CH/DB/RS
AA3202MW/MB/MT/CH/DB/RS
AA3203MW/MB/MT/CH/DB/RS



AA3140MW/MB/MT
AA3140CH/DB/RS



AA3141MW/MB/MT
AA3141CH/DB/RS



AA3207MW/MB/MT/CH/DB/RS
AA3208MW/MB/MT/CH/DB/RS
AA3209MW/MB/MT/CH/DB/RS


1. USE

British standard single and double pole socket outlets, switched and shuttered 1-gang and 2-gang mechanisms with rocker, need to be equipped with special plate.
Installation in 1-gang or 2-gang box 35 mm deep (minimum), in place of a standard product screw fixing


2. RANGE

Description	Type	Matt White	Matt Black	Matt Titanium	Champagne	Dark Bronze	Rose
1 GANG BS 13A 2P+E SP SW SKT	1-gang	AA3201MW	AA3201MB	AA3201MT	AA3201CH	AA3201DB	AA3201RS
1 GANG BS 13A 2P+E DP SW SKT	1-gang	AA3202MW	AA3202MB	AA3202MT	AA3202CH	AA3202DB	AA3202RS
1 GANG BS 13A 2P+E SP SW SKT + LED	1-gang	AA3203MW	AA3203MB	AA3203MT	AA3203CH	AA3203DB	AA3203RS
1 GANG BS 13A 2P+E UNSW SKT	1-gang	AA3140MW	AA3140MB	AA3140MT	AA3140CH	AA3140DB	AA3140RS
2 GANG BS 13A 2P+E UNSW SKT	2-gang	AA3141MW	AA3141MB	AA3141MT	AA3141CH	AA3141DB	AA3141RS
2 GANG BS 13A 2P+E SP SW SKT	2-gang	AA3207MW	AA3207MB	AA3207MT	AA3207CH	AA3207DB	AA3207RS
2 GANG BS 13A 2P+E SP SW SKT + LED	2-gang	AA3208MW	AA3208MB	AA3208MT	AA3208CH	AA3208DB	AA3208RS
2 GANG BS 13A 2P+E SP SW SKT + LED	2-gang	AA3209MW	AA3209MB	AA3209MT	AA3209CH	AA3209DB	AA3209RS

3. DIMENSIONS (mm)



References	A	B	C	D
AA3201MW/MB/MT/CH/DB/RS AA3202MW/MB/MT/CH/DB/RS AA3203MW/MB/MT/CH/DB/RS	78.5	83.5	30.8	20
AA3140MW/MB/MT/CH/DB/RS	78.5	83.5	28	20



References	A	B	C	D
AA3141MW/MB/MT/CH/DB/RS	83.5	143.5	27.3	19.3
AA3207MW/MB/MT/CH/DB/RS AA3209MW/MB/MT/CH/DB/RS	83.5	143.5	29.6	18.5
AA3208MW/MB/MT/CH/DB/RS	83.5	143.5	29.4	18.5

4. CONNECTION

Types of terminals: with screws
Terminal capacity: $3 \times 4 \text{ mm}^2$
Stripping length: 12mm
Compatible with flexible or rigid cables

5. TECHNICAL CHARACTERISTICS

■ 5.1 Mechanical characteristics

Impact test: IK04
Protection against solids & liquids: IP20

■ 5.2 Material characteristics

Rocker: PC
Frame: PC
Base: PC
Self-extinguishing:
+ 850°C / 30 s for insulating parts holding live parts in place
+ 650°C / 30 s for other parts made of insulating materials

■ 5.3 Electrical characteristics

Voltage: 250V~
Current: 13A

■ 5.4 Climatic characteristics

Usage temperature: -5°C to +35°C
Storage temperature: -10°C to +70°C

6. CARE

Clean the surface with a cloth.

Do not use acetone, tar-removing cleaning agents or trichloroethylene.

Resistant to the following products: Hexane, methylated spirit, soapy water, diluted ammonia, bleach diluted to 10%, window-cleaning products, pre-impregnated wipes.

Caution: Always test before using special cleaning products.

7. STANDARDS AND APPROVALS

Conform to IEC 60884-1 standard