



Arteor™ Advance with Netatmo - British Standard Smart ON/OFF wireless controls for lighting and socket outlets


Cat. No(s): AC5201MW/MB/MT AA5201MW/MB/MT
 AC5202MW/MB/MT AA5202MW/MB/MT
 AC5203MW/MB/MT AA5203MW/MB/MT




AC5201MW/MB/MT




AC5202MW/MB/MT




AC5203MW/MB/MT



AA5201MW/MB/MT



AA5202MW/MB/MT



AA5203MW/MB/MT

1. USE

Wireless controls for ON/OFF/dimming light functions or connected socket outlets.

Requires the prior installation of a smart Gateway for connected installation or a Control module "with Netatmo".

This product controls "with Netatmo" micromodule products, smart socket outlets and smart switches.

Can be used as a two-way switch or to control a lighting group.

- Fixes directly on the wall or screws onto a flush-mounting box.
- Fits on furniture (movable).

1-gang can be combined with 20 wired products.


2-gang can be combined with 2 x 20 wired products.

3-gang can be combined with 3 x 20 wired products.


2. RANGE

Description	Matt White	Matt Black	Matt Titanium
Smart ON/OFF wireless controls with battery. Supplied with a secable support frame and a rocker. Equipped with an LED indicator (configuration) and a RESET button (hidden) used to return to factory settings. Repositionable self-adhesive fixings (supplied). To be equipped with finishing plate.	AC5201MW AA5201MW 1-gang	AC5201MB AA5201MB 1-gang	AC5201MT AA5201MT 1-gang
	AC5202MW AA5202MW 2-gang	AC5202MB AA5202MB 2-gang	AC5202MT AA5202MT 2-gang
	AC5203MW AA5203MW 3-gang	AC5203MB AA5203MB 3-gang	AC5203MT AA5203MT 3-gang

3. DIMENSIONS (mm)





A	B	B'	C
86	123	86	11.8





A	B	B'	C
86	123	86	12.1

4. OPERATION



1-gang: AC5201MW/MB/MT
 AA5201MW/MB/MT



2-gang: AC5202MW/MB/MT
 AA5202MW/MB/MT



3-gang: AC5203MW/MB/MT
 AA5203MW/MB/MT



5. TECHNICAL CHARACTERISTICS

■ **5.1 Mechanical characteristics**

Protection against impacts: IK 02
 Protection against solid bodies and/or liquids: IP 20

■ **5.2 Material characteristics**

Rocker: PC
 Mechanism casing with grid: Fibreglass-reinforced (20%) PC
 Halogen-free
 UV-resistant
 Self-extinguishing: 650°C/30 s

■ **5.3 Electrical characteristics**

Powered by a CR2032 - 3 V lithium battery (supplied)
 Battery life: 8 years for 10 activations a day

ZigBee radio technology

frequency: 2.4 GHz to 2.4835 GHz
 Power level: < 100 mW

■ **5.4 Climate characteristics**

Storage temperature: 0° C to + 45° C
 Usage temperature: +5° C to + 35° C

6. CARE

Clean the surface with a cloth.
 Do not use acetone, tar-removing cleaning agents or trichloroethylene.

Resistant to the following products:
 Hexane, methylated spirit, soapy water, diluted ammonia, bleach diluted to 10%, window-cleaning products, pre-impregnated wipes.

Caution: Always test before using special cleaning products.



Take care to recycle the battery appropriately.

7. STANDARDS AND APPROVALS

Compliant with installation and manufacturing standards.
 The undersigned, LEGRAND, declares that the radio-electric equipment type (AC5201MW/MB/MT, AC5202MW/MB/MT, AC5203MW/MB/MT, AA5201MW/MB/MT, AA5202MW/MB/MT, AA5203MW/MB/MT) complies with directive 2014/53/EU.
 The full text of the EU declaration of conformity is available on the following website: www.legrand.com/ecatalogue