



Niloé™ Cover plates


Cat. No(s): NP111BK/DB/GR/MA/MG/OL/WH,
NP112BK/DB/GR/MA/MG/OL/WH, NP113BK/DB/GR/MA/MG/
OL/WH, NP114BK/DB/GR/MA/MG/OL/WH,
NP115BK/DB/GR/MA/MG/OL/WH, NP117WH



NP111..



NP112..



NP117..

1. USE

Faceplates for Niloé from 1 to 5 gangs wiring accessories.
Available in several colours.

2. RANGE

1-gang plates with labelholder


	White	NP117WH
---	-------	---------

1-gang plates

	White Medium grey Black Dark bronze Dark grey Mastic Olive	NP111WH NP111MG NP111BK NP111DB NP111GR NP111MA NP111OL
---	--	---

2-gang plates


71 mm spacing - horizontal and vertical

	White Medium grey Black Dark bronze Dark grey Mastic Olive	NP112WH NP112MG NP112BK NP112DB NP112GR NP112MA NP112OL
---	--	---

2. RANGE (continued)


3-gang plates

71 mm spacing - horizontal and vertical

	White Medium grey Black Dark bronze Dark grey Mastic Olive	NP113WH NP113MG NP113BK NP113DB NP113GR NP113MA NP113OL
--	--	---


4-gang plates

71 mm spacing - horizontal and vertical


	White Medium grey Black Dark bronze Dark grey Mastic Olive	NP114WH NP114MG NP114BK NP114DB NP114GR NP114MA NP114OL
--	--	---

5-gang plates

71 mm spacing - horizontal and vertical

	White Medium grey Black Dark bronze Dark grey Mastic Olive	NP115WH NP115MG NP115BK NP115DB NP115GR NP115MA NP115OL
--	--	---

3. OVERALL DIMENSIONS (mm)



References	A	B	C
1-gang, 1-gang with labelholder	86	86	10.1
2-gang 71 mm fixing centres	86	157	10.1
3-gang 71 mm fixing centres	86	228	10.1
4-gang 71 mm fixing centres	86	299	10.1
5-gang 71 mm fixing centres	86	370	10.1

4. TECHNICAL CHARACTERISTICS

■ 4.1 Materials

Polygloss appearance: molded white
Mat surface appearance: painted colors
Material: - ABS plate
 - Halogen-free
 - UV resistant

Self-extinguishing:
+ 850°C/30 s for insulating parts holding live parts in place
+ 650°C/30 s for other parts made of insulating materials

■ 4.2 Climatic characteristics

Storage temperature: - 10° C to +70° C
Usage temperature: - 5° C to +40° C

5. CLEANING

Clean the surface with a cloth.
Do not use acetone, tar-removing cleaning agents or trichloroethylene.

Caution: An initial test is required for the use of other special maintenance products.

7. STANDARDS AND APPROVALS

The undersigned, LEGRAND, declares that the radio-electric equipment type (Cat. Nos NP111BK/DB/GR/MA/MG/OL/WH - NP112BK/DB/GR/MA/MG/OL/WH - NP113BK/DB/GR/MA/MG/OL/WH - NP114BK/DB/GR/MA/MG/OL/WH - NP115BK/DB/GR/MA/MG/OL/WH - NP117WH) complies with directive 2014/53/EU.
The full text of the EU declaration of conformity is available on the following website: www.legrand.com/ecatalogue