


Surface-mounted equipment One way or tow way switch




1. USE

Lighting control mechanisms including or not identification elements (lights) or signaling elements (markings).


Lighting control mechanisms with feasible functions:

- _ Simple one way switch.
- _ Simple two way switch.

2. RANGE

		References
Configurable		0 861 15LA

3. OVERALL DIMENSIONS (mm)



	A	B	C
Configurable	53.5	54.7	29.5

4. CONNECTION

Type of terminals: automatic

Terminal capacity: 1.5 mm² - 2.5 mm² (1 or 2 conductors)

Stripping length: 12 mm

5. TECHNICAL CHARACTERISTICS

■ 5.1 Protection index

Protection against solid bodies and liquids: IP 31D

Protection against impact: IK 04

■ 5.2 Material characteristics

Frame, support : PS

Rocker: ABS

Mechanism: PC

UV-resistant

Halogen-free

Self-extinguishing:

850°C/30 s for insulating components holding live parts in place.

650°C/30 s for other insulating components.

■ 5.3 Electrical characteristics


Voltage: 250 V~

Frequency: 50 Hz

Current: 10 AX

Maximum power on lamps with integrated ballast

(LED lamps and compact fluorescent): 100 W



■ 5.4 Climate characteristics

Usage temperature: - 10° to + 40° C

Storage temperature: - 25° C to + 60° C

6. CLEANING

Surface cleaning with a cloth.

Do not use: acetone, tar remover, trichloroethylene.

Maintenance with the following products: Hexane (EN 60669-1), Methylated spirit, Soapy water, Diluted ammonia, Bleach diluted to 10%, Window-cleaning products, Pre-saturated wipes.

Caution: A preliminary test should be carried out if other specific cleaning products are to be used.

7. STANDARDS AND APPROVALS

Compliance with standards of installation and manufacturing.

Refer to e. catalogue.