


Valena™ Next Smart ON/OFF switch without neutral

Cat. No(s): 741201 - 741301 - 741401



1. USE

Smart ON/OFF switch without neutral.

Can be combined with one or more wireless lighting controls and/or mechanical push-buttons or toggle switches.
For local or remote control of your lighting.
Easy to install in place of a standard switch in a box 40 mm deep (minimum).
Fixing with claws and/or screws.


2. RANGE

Description

Product for use in conjunction with the starter pack "with Netatmo".
With LED indicator (configuration) and RESET button (hidden) used to return in factory settings.
Delivered with protection cover.
To be equipped with plate.

White	Aluminium	Dark
741201	741301	741401

3. DIMENSIONS (mm)




A	B	C	D
74	74	45	10

4. CONNECTION

Terminal type : with screws
Terminal capacity: 1 x 2.5 mm² - 2 x 1.5 mm²
Stripping length: 7 mm
Screwdriver: 3 mm

5. OPERATION



6. TECHNICAL CHARACTERISTICS

■ 6.1 Mechanical characteristics

Protection against impacts: IK 04
Protection against solid bodies and liquids: IP 20

■ 6.2 Material characteristics

Mechanism casing: PC
Support: PA 6.6 + Galfan Steel
Rocker plate: painted ABS
Halogen-free
UV-resistant
Self-extinguishing:
850°C/30 s for insulating components holding live parts in place.
650°C/30 s for other insulating components.

■ 6.3 Climate characteristics

Usage temperature: + 5°C to +35°C
Storage temperature: 0°C to +45°C

6. TECHNICAL CHARACTERISTICS *(continued)*

■ 6.4 Electrical characteristics

Voltage: 110/240 V~

Power: 200 W

Standby consumption: 1.5 mA

The smart switch without neutral works with standard bulbs including LED.

Frequency bands: 2.4 GHz to 2.4835 GHz

Power level: < 100 mW

Range: 200 m of unobstructed space

10 m between products indoors

7. ACCESSORY

Supplied with an active compensator (Cat. No 0 401 29), mandatory for optimum operation with market lamps.
Only one compensator per lighting circuit.

8. CARE

Clean the surface with a cloth.

Do not use acetone, tar-removing cleaning agents or trichloroethylene.

Resistant to the following products: Hexane, methylated spirit, soapy water, diluted ammonia, bleach diluted to 10%, window-cleaning products, pre-impregnated wipes.

Caution: Always test before using special cleaning products.

9. STANDARDS AND APPROVALS

Compliant with installation and manufacturing standards.

See e-catalogue.

The undersigned, LEGRAND, declares that the radio-electric equipment type (741201 - 741301 - 741401) complies with directive 2014/53/EU.

The full text of the EU declaration of conformity is available on the following website: **www.legrand.com/ecatalogue**