


Arteor™ Advance 45A cooker control unit

Cat. No(s): AA730MW/MB/MT



AA730MW/MB/MT

1. USE

High capacity double pole switches for the control of fixed appliances eg. cooker ovens, shower or air-conditioning units, Version available with LED "power on" indicator.

Need to be equipped with special plate.


Supplied with M3.5 screws for Flush mounting or surface mounting BS boxes.

Box depth ≥ 35 mm

2. RANGE

Description	Type	Matt White	Matt Black	Matt Titanium
45A COOKER UNIT CONTROL	2-gang	AA730MW	AA730MB	AA730MT

3. DIMENSIONS (mm)



References	A	B	C	D
AA730MW/MB/MT	83.5	143.5	33.9	19.9

4. CONNECTION

Types of terminals: with screws

Terminal capacity: $2 \times 6 \text{ mm}^2$ or $1 \times 10 \text{ mm}^2$

Stripping length: 24 mm L/N and 8mm Earth

Screwdriver size: < 4 mm flat blade

5. TECHNICAL CHARACTERISTICS

■ 5.1 Mechanical characteristics

Impact test: IK04

Protection against solids & liquids: IP20

■ 5.2 Material characteristics

Rocker: PC

Frame: PC

Base: PC

Self-extinguishing:

+ 850° C / 30 s for insulating parts holding live parts in place

+ 650° C / 30 s for other parts made of insulating materials

■ 5.3 Electrical characteristics

Voltage: 250V~

Current: switch 45A / socket 13A

■ 5.4 Climatic characteristics

Usage temperature: -5°C to +35°C

Storage temperature: -10°C to +70°C

6. CARE

Clean the surface with a cloth.

Do not use acetone, tar-removing cleaning agents or trichloroethylene.

Resistant to the following products: Hexane, methylated spirit, soapy water, diluted ammonia, bleach diluted to 10%, window-cleaning products, pre-impregnated wipes.

Caution: Always test before using special cleaning products.

7. CONFORMITY - APPROVALS

Conform to BS4177 & BS1363-2 standards