


Arteor™ Advance Plates British Standard Decor Collection

Cat. No(s): AC1100FW/FB/DA/BS/BB/AB - AC1102FW/FB/DA/BS/BB/AB - AC1104FW/FB/DA/BS/BB/AB
AC1105FW/FB/DA/BS/BB/AB - AC1108FW/FB/DA/BS/BB/AB - AC1204FW/FB/DA/BS/BB/AB
AC1206FW/FB/DA/BS/BB/AB - AC1209FW/FB/DA/BS/BB/AB - AA1104FW/FB/DA/BS/BB/AB
AA1105FW/FB/DA/BS/BB/AB - AA1107FW/FB/DA/BS/BB/AB - AA1108FW/FB/DA/BS/BB/AB
AA1109FW/FB/DA/BS/BB/AB - AA1106FW/FB/DA/BS




1. USE

Finishing plates.
The plates clip into notches on screw and/or claw fixings.
Protection film must be removed only once site work is fully completed.

2. RANGE

Designation	Finishes					
Decor Collection	Frosted White	Frosted Black	Dark Aluminium	Brushed Stainless Steel	Brushed Bronze	Brushed Antique Brass
Square Version						
1 module - 1 gang	AC1100FW	AC1100FB	AC1100DA	AC1100BS	AC1100BB	AC1100AB
2 modules - 1 gang	AC1102FW	AC1102FB	AC1102DA	AC1102BS	AC1102BB	AC1102AB
3 modules - 1 gang	AC1104FW	AC1104FB	AC1104DA	AC1104BS	AC1104BB	AC1104AB
3 modules - 2 gang	AC1105FW	AC1105FB	AC1105DA	AC1105BS	AC1105BB	AC1105AB
2x2 modules - 2 gang	AC1108FW	AC1108FB	AC1108DA	AC1108BS	AC1108BB	AC1108AB
6 modules	AC1204FW	AC1204FB	AC1204DA	AC1204BS	AC1204BB	AC1204AB
8 modules	AC1206FW	AC1206FB	AC1206DA	AC1206BS	AC1206BB	AC1206AB
2x6 modules	AC1209FW	AC1209FB	AC1209DA	AC1209BS	AC1209BB	AC1209AB
Slender version						
1 module - 1 gang	AA1104FW	AA1104FB	AA1104DA	AA1104BS	AA1104BB	AA1104AB
2x1 modules - 1 gang	AA1105FW	AA1105FB	AA1105DA	AA1105BS	AA1105BB	AA1105AB
3x1 modules - 1 gang	AA1106FW	AA1106FB	AA1106DA	AA1106BS	-	-
For rotary dimmers, fan controls and USB chargers - 1 gang	AA1107FW	AA1107FB	AA1107DA	AA1107BS	AA1107BB	AA1107AB
3x1 modules - 2 gang	AA1108FW	AA1108FB	AA1108DA	AA1108BS	AA1108BB	AA1108AB
4x1 modules - 2 gang	AA1109FW	AA1109FB	AA1109DA	AA1109BS	AA1109BB	AA1109AB

3. DIMENSIONS (mm)



Cat. Nos	A	B	C
AA1104FW/FB/DA/BS/BB/AB AA1105FW/FB/DA/BS/BB/AB AA1106FW/FB/DA/BS AA1107FW/FB/DA/BS/BB/AB AC1100FW/FB/DA/BS/BB/AB AC1102FW/FB/DA/BS/BB/AB AC1104FW/FB/DA/BS/BB/AB	90	90	8,5
AA1108FW/FB/DA/BS/BB/AB AA1109FW/FB/DA/BS/BB/AB AC1105FW/FB/DA/BS/BB/AB AC1108FW/FB/DA/BS/BB/AB	90	157	8,5
AC1204FW/FB/DA/BS/BB/AB	90	237,5	8,5
AC1206FW/FB/DA/BS/BB/AB	90	252,5	8,5
AC1209FW/FB/DA/BS/BB/AB	178	237,5	8,5

4. TECHNICAL CHARACTERISTICS

■ 4.1 Mechanical characteristics

Impact test: IK 02

■ 4.2 Material characteristics

Underplate : PC

Finishes for FW/FB: PC

for BS/BB/AB: metal

for DA: metal + composite based

Self-extinguishing: 650°C/30 s

■ 4.3 Climate characteristics

Storage temperature: - 10° c to + 70° C

Usage temperature: - 5° C to + 35° C

5. CLEANING

Surface cleaning with a cloth.

Do not use: acetone, tar remover, trichloroethylene.

Resistance to the following agents: Hexane.

Methylated spirits, Soapy water, diluted ammonia, diluted pure bleach
10%, Glass cleaning substance, Pre-impregnated wipes.

Caution: Always test before using other special cleaning products.

6. STANDARDS AND APPROVALS

Compliance with installation and manufacturing standards.

Refer to e-catalogue.