


Niloé™ STEP IP44 plate

Cat. No(s): 3 982 70, 8 63X 96, 8 640 71



3 982 70, 8 63X 96, 8 640 71


1. USE

Faceplates IP 44 for Niloé Step for 1 gangs wiring accessories.
Available in several colours.

2. RANGE

Description	White	Aluminium	Medium Grey	Black
IP44 plate	3 982 70, 8 631 96, 8 640 71	8 633 96	8 634 96	8 635 96

3. DIMENSIONS (mm)



A	B	C
75.8	75.8	23.2

4. MOUNTING

The plates snap onto the socket adapter or the switch cover. In case of the sockets, the socket cover clamp the frame.

5. TECHNICAL CHARACTERISTICS

■ 5.1 Mechanical characteristics
180° opening capacity of the cover
Impact tests: IK 04
Penetration against solid bodies and liquids: IP 44

■ 5.2 Material characteristics
Plates: ABS
Shutter for plate: PC
UV resistant
Halogen free
Sealing material: SEBS
Self-extinguishing: 650° C / 30 s

■ 5.3 Climatical characteristics
Storage temperature: - 10° C to +70° C
Usage temperature: - 5° C to + 40° C

6. CLEANING

Surface cleaning with a cloth. Do not use: acetone, tar remover, trichloroethylene.

■ 6.1 Resistance to the following cleaning substances

- Hexane
- Methylated spirit,
- Soapy water,
- Diluted ammonia,
- Diluted pure bleach 10%,
- Glass cleaning product,
- Pre-impregnated wipes.

Caution: Always test before using other special cleaning products.

7. SPECIAL USE

The plates must not be painted.

8. STANDARDS AND APPROVALS

The undersigned, LEGRAND, declares that the radio-electric equipment type (Cat. No 3 982 70 - 8 631 96 - 8 633 96 - 8 634 96 - 8 635 96 - 8 640 71) complies with directive 2014/53/EU.

The full text of the EU declaration of conformity is available on the following website: www.legrand.com/ecatalogue