



Arteor™ Advance

Cat. No(s): AC426MW/MB/MT
AC427MW/MB/MT

Telephone Socket



AC426MW/MB/MT



AC427MW/MB/MT


1. USE

Telephone socket outlet for the transmission telephone signals.

2. RANGE

Description	Type	Matt White	Matt Black	Matt Titanium
1 MODULE SINGLE SECONDARY TELEPHONE SOCKET	1M	AC426MW	AC426MB	AC426MT
2 MODULES SINGLE MASTER TELEPHONE SOCKET	2M	AC427MW	AC427MB	AC427MT

3. DIMENSIONS (mm)



References	A	B	C	D
AC426MW/MB/MT	45	22.5	35	24.2
AC427MW/MB/MT	45	45	15.95	26.65

4. CONNECTION

Types of terminals: with screws
Terminal capacity: 1 x 0.4 ~ 0.8 mm² (or 24 - 26 AWG)
Stripping length: 6 - 8 mm
Screwdriver size: ≤ 3.5 mm flat blade

5. TECHNICAL CHARACTERISTICS

■ 5.1 Mechanical characteristics

Impact test: IK04
Protection against solids & liquids: IP20

■ 5.2 Material characteristics

Cover: PC
Base: PC
Self-extinguishing:
+ 850° C / 30 s for insulating parts holding live parts in place
+ 650° C / 30 s for other parts made of insulating materials

■ 5.3 Electrical characteristics

Voltage: 150V ~
Current: 2A
Insulation resistance: ≥ 1000 MΩ
Dielectric strength: 1500 V ~, 1 min

■ 5.4 Climatic characteristics

Usage temperature: -10°C to +35°C
Storage temperature: -10°C to +70°C

6. CARE

Clean the surface with a cloth.
Do not use acetone, tar-removing cleaning agents or trichloroethylene.

Resistant to the following products: Hexane, methylated spirit, soapy water, diluted ammonia, bleach diluted to 10%, window-cleaning products, pre-impregnated wipes.

Caution: Always test before using special cleaning products.

7. CONFORMITY - APPROVALS

Compliant with installation and manufacturing standards, see e-catalogue.