


Céliane™

Cat. No(s): CM0153

2 USB Type-A + Type-C - 15W



CM0153


1. USE

Allows you to power and charge multimedia terminals: tablets and smartphones (Android, Apple).

2. RANGE

2 USB Type-A + Type-C / 15 W	Cat. Nos
To be equipped with support frame, face plate and finishing plate 2 modules - 40 mm deep minimum	CM0153

3. DIMENSIONS (mm)



A	B	C	D
45	45	42	8,5

4. CONNECTION

Type of terminals: with screws
Terminal capacity: 2 x 2.5 mm²
Stripping length: 6 mm
Screwdriver: flat 3.5 mm

5. TECHNICAL CHARACTERISTICS

■ 5.1 Mechanical characteristics

Impact tests: IK 04
Penetration by solid bodies and liquids: IP 40

■ 5.2 Material characteristics

PC
Halogen-free
UV resistant
Self-extinguishing:
850° C/30 s for insulating parts holding live parts in place
650° C/30 s for other parts made of insulating materials

■ 5.3 Climatic characteristics

Storage temperature: - 20°C to + 70°C
Usage temperature: + 5°C to + 35°C

■ 5.4 Electrical characteristics

All values listed below are measured at an ambient temperature of + 20° and after 30 minutes of operation.

Nominal input voltage	100-240 V~
Nominal input frequency	50-60 Hz
Max. output power	15 W
Nominal input current	0.3 A
Max. nominal output current Type-A + Type-C	3.0 A shared on A and C output
Max. nominal output current Type-C	3.0 A
Stand-by power consumption	0.07 W
Nominal output voltage	5 V~ *
Average efficiency in active mode	80.3%
Consumption class without load and average level of efficiency	Level VI
Protection class	II - Low voltage

Note: To optimize the charging time of your device, ensure turn it off during the charging phase.

6. CLEANING

Surface cleaning with a cloth.

Do not use: acetone, tar remover, trichloroethylene.

Resistance to the following agents:

Hexane, methylated spirits, soapy water, diluted ammonia, pure bleach diluted to 10%, window-cleaning products, pre-impregnated wipes.

Caution: Always test before using other special cleaning products

7. STANDARDS AND APPROVALS

Compliant with installation and manufacturing standards.

Refer to e-catalogue.