


Niloé™ STEP Buzzer

Cat. No(s): 8 641 88B - 8 643 88B - 8 645 88B



8 64X 88B

1. USE

Electrical signaling device used for notifications, alarms, and industrial applications.

Supplied with support frame cover plates and without plates.

Mechanisms supplied with protection cover.


To be equipped with plates one or several gangs.

Screw or claw fixing.

2. RANGE

Description	White	Aluminium	Black
Buzzer	8 641 88B	8 643 88B	8 645 88B

3. DIMENSIONS (mm)



A	B	C	D
75.8	75.8	30	10

4. CONNECTION

Type of terminals: with screws

Terminal capacity: 2 x 2.5 mm²

Stripping length (mm): 8 mm

Flexible or rigid cables compatible

5. TECHNICAL CHARACTERISTICS

■ 5.1 Mechanical characteristics

Protection against solid bodies and liquids: IP 20

Protection against impact: IK 04

■ 5.2 Material characteristics

Material : - Mechanism housing: PC

- Halogen free

Material of the support: - PC grey RAL 7016 + 10 % glass fiber

- Halogen free

Self-extinguishing:

+ 850° C / 30 s for insulating parts holding live parts in place

+ 650° C / 30 s for other parts made of insulating materials

■ 5.3 Electrical characteristics

• Voltage: 110 - 240 V~

• Frequency: 50/60 Hz

■ 5.4 Climatic characteristics

Storage temperature: - 10° C to +70° C

Usage temperature: - 5° C to + 40° C

6. MAINTENANCE

Surface cleaning with a cloth.

Do not use: acetone, tar remover, trichloroethylene.

Maintenance with the following products: Hexane, Methylated spirit,

Soapy water, Diluted ammonia, Bleach diluted to 10%,

Window-cleaning products.

Caution: A preliminary test should be carried out if other specific cleaning products are to be used.

7. STANDARDS AND APPROVALS

The undersigned, LEGRAND, declares that the radio-electric equipment type (Cat. Nos 8 641 88B - 8 643 88B - 8 645 88B) complies with directive 2014/53/EU. The full

text of the EU declaration of conformity is available on the following website: www.legrand.com/ecatalogue