


# Céliane™

## 2 USB Type-A + Type-C - 20W - Power Delivery

Cat. No(s): CM0155



CM0155

### 1. USE


Allows you to power and charge multimedia terminals: tablets and smartphones (Android, Apple) with or without Power Delivery technology.

Optimises the charging speed of terminals compatible with **USB Power Delivery and Quick Charge protocols.**

### 2. RANGE

<b>2 USB Type-A + Type-C / 20 W - Power Delivery</b>	<b>Cat. Nos</b>
To be equipped with support frame, face plate and finishing plate 2 modules - 40 mm deep minimum	CM0155

### 3. DIMENSIONS (mm)



<b>A</b>	<b>B</b>	<b>C</b>	<b>D</b>
45	45	33	8,5

### 4. CONNECTION

Type of terminals: with screws  
 Terminal capacity: 2 x 2.5 mm<sup>2</sup>  
 Stripping length: 6 mm  
 Screwdriver: flat 3.5 mm

### 5. TECHNICAL CHARACTERISTICS

#### ■ 5.1 Mechanical characteristics

Impact tests: IK 04  
 Penetration by solid bodies and liquids: IP 40

#### ■ 5.2 Material characteristics

PC  
 Halogen-free  
 UV resistant  
 Self-extinguishing:  
 850° C/30 s for insulating parts holding live parts in place  
 650° C/30 s for other parts made of insulating materials

#### ■ 5.3 Climatic characteristics

Storage temperature: - 20°C to + 70°C  
 Usage temperature: + 5°C to + 35°C

#### ■ 5.4 Electrical characteristics

All values listed below are measured at an ambient temperature of + 20° and after 30 minutes of operation.

Nominal input voltage	100-240 V~
Nominal input frequency	50-60 Hz
Max. output power	20 W
Nominal input current	0.5 A
Max. nominal output current	3.0 A
Stand-by power consumption	0.04 W
Nominal output voltage	5 V... *
Average efficiency in active mode	87 %
Consumption class without load and average level of efficiency	Level VI
Protection class	II - Low voltage

#### Optimise / voltage \*

1 output - Type A		1 output - Type C		2 output	
5.0 V	3.0 A	5.0 V	3.0 A	Type A : 5.0 V	1.5 A
9.0 V	2.0 A	9.0 V	2.2 A	Type C : 5.0 V	1.5 A
12.0 V	1.5 A	12.0 V	1.6 A		

**Note:** To optimize the charging time of your device, ensure turn it off during the charging phase.

## 6. CLEANING

Surface cleaning with a cloth.

Do not use: acetone, tar remover, trichloroethylene.

Resistance to the following agents:

Hexane, methylated spirits, soapy water, diluted ammonia, pure bleach diluted to 10%, window-cleaning products, pre-impregnated wipes.

**Caution:** Always test before using other special cleaning products

## 7. STANDARDS AND APPROVALS

Compliant with installation and manufacturing standards.

Refer to e-catalogue.