

Freestanding and modular industrial enclosures XL³ HP 6300

Cat. Nos: see catalogue pages



CONTENTS	Pages
1. General characteristics	1
2. Range	1
3. Dimensions	1
4. Technical characteristics	3
5. Maintenance	5
6. Equipment	6
7. Accessories	9
8. 19" accessories	11
9. Standards and regulations	11
10. Other information	11

1. GENERAL CHARACTERISTICS

The XL³ HP 6300 enclosures are suitable for power distribution and automation equipment

2 versions are available :

- freestanding : delivered assembled with a flat metal door and bottom vent, equipped with cable entry plates. For automation applications.

- modular : to be assembled from a roof-base set, uprights, rear panel, side panels, plinth, and a door. For automation, power distribution, or VDI applications.

IP 55 - IK 10 with excellent resistance to corrosion and chemical agents, suitable for use in industrial or dusty environments.

2. RANGE

■ 2.1 Structure of modular enclosures

- Structural uprights (4 vertical uprights): 2 in RAL 7035 and 2 in galvanized steel, with markings indicating the mounting positions for equipment (markings corresponding to the XLPro4 6300 software) :

heights 1200 mm, 1600 mm, 1800 mm, 2000 mm, or 2200 mm

- Roof-base units in grey RAL 7004, equipped with earth connections and cable entry plates at the bottom :

depth 400 mm, 500 mm, 600 mm, 800 mm, 1000 mm, or 1200 mm
width 400 mm, 600 mm, 800 mm, 1000 mm, 1200 mm, 1600 mm

- Rear and side panels in grey RAL 7035, supplied with 2 retaining clips for easy installation

Can be fitted with a plinth, height 100 mm.

■ 2.2 Structure of freestanding enclosures

Welded frame structure in RAL 7035 with removable rear panel. Can be fitted with a plinth, height 100 mm.

■ 2.3 Door

- Flat metal or glass door

- Reversible door, grey RAL 7035, without dismantling the locking rods (2-point locking system, top and bottom).

Supplied with a simple handle with double-bar insert; interchangeable cylinders to be ordered separately

- 1 or 2 doors depending on the enclosure width

3. DIMENSIONS

■ 3.1 Freestanding enclosures

Cat.Nos	H (mm)	W (mm)	D (mm)	Number of doors	Weight (kg)	
3SMA060040160	1600	600	400	1	59,4	
3SMA080040160	1600	800		1	70,1	
3SMA100040160	1600	1000		1	50,6	
3SMA1000401602P	1600	1000		2	86,8	
3SMA120040160	1600	1200		2	99,3	
3SMA060040180	1800	600		1	65,5	
3SMA080040180	1800	800		1	77,3	
3SMA100040180	1800	1000		1	89,0	
3SMA1000401802P	1800	1000		2	95,6	
3SMA120040180	1800	1200		2	109,2	
3SMA160040180	1800	1600		2	135,3	
3SMA080040200	2000	800		1	84,4	
3SMA100040200	2000	1000		1	97,2	
3SMA1000402002P	2000	1000		2	104,4	
3SMA120040200	2000	1200		2	119,0	
3SMA160040200	2000	1600		2	147,5	
3SMA060050180	1800	600	500	1	71,5	
3SMA080050180	1800	800		1	83,5	
3SMA100050180	1800	1000		1	95,4	
3SMA120050180	1800	1200		2	116,4	
3SMA080050200	2000	800		1	91,1	
3SMA100050200	2000	1000		1	104,1	
3SMA120050200	2000	1200		2	126,7	
3SMA160050200	2000	1600		2	155,6	
3SMA080060180	1800	800		600	1	89,7
3SMA080060200	2000	800			1	97,9
3SMA120060200	2000	1200	2		134,5	

3. DIMENSIONS (continued)

3.2 Modular enclosures

Roof-base set + uprights + rear panel				Solid door	Glass door	Side panel (x 1)	Side + front plinth
H (mm)	W (mm)	D (mm)	Weight (kg)	Weight (kg)	Weight (kg)	Weight (kg)	Weight (kg)
1200	400	400	29,2	10,7	-	4,8	4,4
		500	31,4	10,7	-	-	4,7
		600	33,5	10,7	-	7,1	5,0
	600	400	35,6	14,9	-	4,8	5,0
		500	38,4	14,9	-	-	5,3
		600	40,9	14,9	-	7,1	5,6
		800	46,2	14,9	-	9,4	6,2
		1000	51,5	14,9	-	-	6,8
	800	400	42,0	19,0	-	4,8	5,6
		500	45,4	19,0	-	-	5,9
		600	48,3	19,0	-	7,1	6,2
		800	54,6	19,0	-	9,4	6,8
1000		60,8	19,0	-	-	7,4	
1600	600	400	41,9	19,8	-	-	5,0
		500	44,7	19,8	-	7,9	5,3
		600	47,2	19,8	-	9,4	5,6
		800	52,5	19,8	-	12,6	6,2
	800	1000	57,8	19,8	-	15,7	6,8
		1200	63,3	19,8	-	18,9	7,4
		400	49,1	25,2	-	-	5,6
		500	52,5	25,2	-	7,9	5,9
	800	600	55,4	25,2	-	9,4	6,2
		800	61,7	25,2	-	12,6	6,8
		1000	67,9	25,2	-	15,7	7,4
		1200	74,4	25,2	-	18,9	8,0
1000	400	56,3	30,6	-	-	6,2	
	500	60,2	30,6	-	7,9	6,5	
	600	63,6	30,6	-	9,4	6,8	
	800	70,8	30,6	-	12,6	7,4	
1200	1000	78,1	30,6	-	15,7	8,0	
	1200	85,5	30,6	-	18,9	8,6	
	400	64,2	-	-	-	6,8	
	500	68,9	-	-	7,9	7,1	
1800	400	600	72,9	-	-	9,4	7,4
		800	81,5	-	-	12,6	8,0
		1000	90,1	-	-	15,7	8,6
	600	400	37,3	16,2	-	7,1	4,4
500		39,5	16,2	-	8,9	4,7	
600		41,6	16,2	-	10,6	5,0	
400		44,8	22,2	12,8	7,1	5,0	
600	500	47,7	22,2	12,8	8,9	5,3	
	600	50,1	22,2	12,8	10,6	5,6	
	800	55,4	22,2	12,8	14,1	6,2	
	1000	60,7	22,2	12,8	17,6	6,8	
800	1200	66,2	22,2	12,8	21,2	7,4	
	400	52,4	28,2	16,4	7,1	5,6	
	500	55,8	28,2	16,4	8,9	5,9	
	600	58,7	28,2	16,4	10,6	6,2	
1200	800	65,0	28,2	16,4	14,1	6,8	
	1000	71,3	28,2	16,4	17,6	7,4	
	1200	77,7	28,2	16,4	21,2	8,0	

Roof-base set + uprights + rear panel				Solid door	Glass door	Side panel (x 1)	Side + front plinth
H (mm)	W (mm)	D (mm)	Weight (kg)	Weight (kg)	Weight (kg)	Weight (kg)	Weight (kg)
1800	1000	400	60,0	34,2 40,7 ⁽¹⁾	20,0	7,1	6,2
		500	63,9	34,2 40,7	20,0	8,9	6,5
		600	67,3	34,2 40,7	20,0	10,6	6,8
		800	74,5	34,2 40,7	20,0	14,1	7,4
		1000	81,8	34,2 40,7	20,0	17,6	8,0
		1200	89,2	34,2 40,7	20,0	21,2	8,6
	1200	400	60,0	46,7 ⁽¹⁾	-	7,1	6,8
		500	63,9	46,7 ⁽¹⁾	-	8,9	7,1
		600	67,3	46,7 ⁽¹⁾	-	10,6	7,4
		800	74,5	46,7 ⁽¹⁾	-	14,1	8,0
		1000	81,8	46,7 ⁽¹⁾	-	17,6	8,6
		1200	89,2	46,7 ⁽¹⁾	-	21,2	9,2
1600	400	89,2	58,7 ⁽¹⁾	-	7,1	8,0	
	500	68,3	58,7 ⁽¹⁾	-	8,9	8,3	
	600	73,0	58,7 ⁽¹⁾	-	10,6	8,6	
	400	39,6	17,9	-	7,9	4,4	
	500	41,9	17,9	-	9,9	4,7	
	600	43,9	17,9	-	11,8	5,0	
2000	400	400	47,6	24,6	14,1	7,9	5,0
		500	50,4	24,6	14,1	9,9	5,3
		600	52,9	24,6	14,1	11,8	5,6
		800	58,2	24,6	14,1	15,7	6,2
	600	1000	63,5	24,6	14,1	19,6	6,8
		1200	68,9	24,6	14,1	23,6	7,4
		400	55,6	31,2	18,1	7,9	5,6
		500	58,9	31,2	18,1	9,9	5,9
	800	600	61,9	31,2	18,1	11,8	6,2
		800	68,1	31,2	18,1	15,7	6,8
		1000	74,4	31,2	18,1	19,6	7,4
		1200	80,9	31,2	18,1	23,6	8,0
1000	400	63,5	37,9 44,9 ⁽¹⁾	22,1	7,9	6,2	
	500	67,5	37,9 44,9 ⁽¹⁾	22,1	9,9	6,5	
	600	70,8	37,9 44,9 ⁽¹⁾	22,1	11,8	6,8	
	800	78,1	37,9 44,9 ⁽¹⁾	22,1	15,7	7,4	
1200	1000	85,3	37,9 44,9 ⁽¹⁾	22,1	19,6	8,0	
	1200	92,8	37,9 44,9 ⁽¹⁾	22,1	23,6	8,6	
	400	72,2	51,6 ⁽¹⁾	-	7,9	6,8	
	500	76,9	51,6 ⁽¹⁾	-	9,9	7,1	
1600	600	80,9	51,6 ⁽¹⁾	-	11,8	7,4	
	800	89,5	51,6 ⁽¹⁾	-	15,7	8,0	
	1000	98,1	51,6 ⁽¹⁾	-	19,6	8,6	
	400	91,9	64,8 ⁽¹⁾	-	7,9	8,0	
1800	500	97,7	64,8 ⁽¹⁾	-	9,9	8,3	
	600	102,5	64,8 ⁽¹⁾	-	11,8	8,6	

(1) two-door version

3. DIMENSIONS (continued)

■ 3.3 Modular enclosures

Roof-base set + uprights + rear panel				Solid door	Glass door	Side panel (x 1)	Side + front plinth
H (mm)	W (mm)	D (mm)	Weight (kg)	Weight (kg)	Weight (kg)	Weight (kg)	Weight (kg)
2200	400	400	42,1	19,6	-	8,7	4,4
		500	44,3	19,6	-	-	4,7
		600	46,4	19,6	-	13,0	5,0
	600	400	50,4	26,9	15,5	8,7	5,0
		500	53,3	26,9	15,5	-	5,3
		600	55,7	26,9	15,5	13,0	5,6
		800	61,0	26,9	15,5	17,2	6,2
		1000	66,3	26,9	15,5	21,5	6,8
		1200	71,8	26,9	15,5	25,9	7,4
	800	400	58,8	34,2	20,0	8,7	5,6
		500	62,2	34,2	20,0	-	5,9
		600	65,1	34,2	20,0	13,0	6,2
		800	71,4	34,2	20,0	17,2	6,8
		1000	77,6	34,2	20,0	21,5	7,4
		1200	84,1	34,2	20,0	25,9	8,0
	1000	400	67,1	41,5 49,2 ⁽¹⁾	24,5	8,7	6,2
		500	71,1	41,5 49,2 ⁽¹⁾	24,5	-	6,5
		600	74,4	41,5 49,2 ⁽¹⁾	24,5	13,0	6,8
		800	81,7	41,5 49,2 ⁽¹⁾	24,5	17,2	7,4
		1000	88,9	41,5 49,2 ⁽¹⁾	24,5	21,5	8,0
		1200	96,4	41,5 49,2 ⁽¹⁾	24,5	25,9	8,6
	1200	400	76,2	56,4	-	8,7	6,8
		500	80,9	56,4	-	-	7,1
		600	84,9	56,4	-	13,0	7,4
800		93,5	56,4	-	17,2	8,0	
1000		102,1	56,4	-	21,5	8,6	
1600	400	97,1	71,0	-	8,7	8,0	
	500	102,9	71,0	-	-	8,3	
	600	107,6	71,0	-	13,0	8,6	

4. TECHNICAL CHARACTERISTICS

■ 4.1 Degree of protection

IP 55 - IK 10

■ 4.2 Material characteristics

Color: Grey RAL 7035, epoxy-polyester powder coating applied by electrostatic spraying, coating thickness 50–70 µm

Rear panel in painted steel sheet, thickness 12/10 mm

Side panels in painted steel sheet, thickness 12/10 mm

Top and base in painted steel sheet, thickness 15/10 mm

Solid metal door in painted steel sheet, thickness 12/10 mm

Glass door in painted steel sheet, thickness 12/10 mm, with tempered glass thickness 4 mm

■ 4.3 Thermal dissipation chart with a maximum permissible current of 6300 A at a Delta T of 30 K.

Determination by testing of the maximum capacity of an enclosure to dissipate heat according to IEC 62208-1 standard.

Configuration 1 (C1): All external surfaces of the enclosure are free and without contact (e.g., floor-standing, frame, or structure mounting).

Configuration 2 (C2): The rear surface is in contact with a wall, all other surfaces are free (typical case of wall-mounted installation).

For other installation configurations, please contact us.

H (mm)	W (mm)	D (mm)	Maximum dissipable power (W)		
			C1	C2	
1200	400	400	311	270	
		500	355	311	
		600	398	351	
	600	400	398	337	
		500	446	382	
		600	494	426	
		800	589	515	
		1000	684	604	
		1200	780	693	
	800	400	485	403	
		500	537	452	
		600	589	501	
		800	693	598	
		1000	798	696	
		1200	902	793	
	1600	600	400	513	430
			500	572	485
			600	631	540
			800	749	651
			1000	868	761
			1200	986	871
		800	400	622	513
			500	686	572
			600	749	632
800			877	750	
1000			1004	869	
1200			1131	988	
1000	400	732	596		
	500	800	659		
	600	868	723		
	800	1004	850		
	1000	1140	977		
	1200	1277	1104		
1200	400	841	679		
	500	914	747		
	600	986	814		
	800	1131	950		
		1000	1277	1085	

4. TECHNICAL CHARACTERISTICS (continued)

■ **4.3 Thermal dissipation chart with a maximum permissible current of 6300 A at a Delta T of 30 K.(continued)**

H (mm)	W (mm)	D (mm)	Maximum dissipation power (W)		
			C1	C2	
1800	400	400	449	384	
		500	509	441	
		600	570	497	
	600	400	570	476	
		500	635	537	
		600	700	597	
		800	830	718	
		1000	960	839	
	800	1200	1089	960	
		400	691	567	
		500	760	632	
		600	830	697	
		800	968	826	
	1000	1000	1107	956	
		1200	1246	1085	
		400	812	659	
		500	886	728	
		600	960	797	
	1200	800	1107	934	
		1000	1255	1072	
		1200	1403	1210	
		400	933	750	
		500	1011	823	
	1600	600	1089	896	
		800	1246	1042	
		1000	1403	1188	
		400	1175	933	
		500	1262	1014	
	2000	400	600	1349	1096
			400	495	422
			500	561	484
		600	600	627	546
			400	627	522
			500	698	588
			600	769	654
			800	910	786
800		1000	1051	918	
		1200	1192	1050	
		400	760	622	
		500	835	692	
		600	910	762	
1000		800	1060	902	
		1000	1210	1042	
		1200	1361	1183	
		400	892	722	
		500	972	796	
1200		600	1051	870	
		800	1210	1019	
		1000	1369	1167	
		1200	1529	1316	
		400	1024	822	
1600		500	1108	900	
		600	1192	978	
		800	1361	1135	
		1000	1529	1292	
		400	1289	1021	
600		500	1382	1108	
		600	1475	1194	

H (mm)	W (mm)	D (mm)	Maximum dissipation power (W)	
			C1	C2
2200	400	400	541	460
		500	613	528
		600	684	595
	600	400	684	569
		500	761	640
		600	837	711
		800	990	854
		1000	1143	996
	800	1200	1296	1139
		400	828	677
		500	909	752
		600	990	827
		800	1152	978
	1000	1000	1313	1129
		1200	1475	1280
		400	972	785
		500	1058	864
		600	1143	944
	1200	800	1313	1103
		1000	1484	1262
		1200	1655	1421
		400	1116	893
		500	1206	976
	1600	600	1296	1060
		800	1475	1228
		1000	1655	1395
		400	1404	1109
		500	1503	1201
	600	600	1601	1293

■ **4.4 Mechanical characteristics**

Maximum load: 1000 kg

■ **4.5 Resistance to climatic conditions**

Storage and installation temperature: -10 °C to +70 °C

Operating temperature: -5 °C to +40 °C

Corrosivity class: C4-L

Indoor installation required

■ **4.6 Seismic Withstand Capability**

Seismic test – Zone 4, K = 1.5 according to IEC 60068-3-3:2019

4. TECHNICAL CHARACTERISTICS (continued)

■ 4.7 Resistance to chemical agents

Aqueous solutions	Cold water	++	
	Hot water	+	
	Steam	-	
	5% Salt water	+	
	Hydrogen peroxide	-	
	Water + detergent	+	
	Water + surfactants	+	
	Formaldehyde	-	
	Alcohols	Ethanol	+
Methanol		+	
Propanol		+	
Butanol		+	
Glycols	Ethylene glycol	+	
Phenols		-	
Cresols		-	
Bases	Ammonia	+	
	Sodium hydroxide (caustic soda)	+	
	Sodium hypochlorite (bleach 12°)	+	
	Potassium hydroxide (potash)	+	
Strong oxidizing acids	Concentrated acetic acid	+	
	Nitric acid 5%	+	
	Sulfuric acid 30%	+	
	Hydrochloric acid 30%	+	
	Perchloric acid 70%	++	
	Hydrofluoric acid 70%	--	
	Chromic acid 50%	-	
Phosphoric acid 30%	+		
Weak acids	Diluted acetic acid < 25 %	+	
	Citric acid	++	
	Lactic acid	++	
	Formic acid	+	
	Uric acid	+	
Oils and fats	Animal origin	Lard	++
		animale	++
	Vegetable origin	Linseed oil	++
		Peanut / Olive	++
		Castor	++
		Glycerin	+
	Mineral origin	Paraffin (vaseline)	++
		Automotive engine oils	+
		Silicone oils	++
		Cutting oils	++
	Hydraulic oils	+	

Hydrocarbons	Unleaded gasoline	+
	Diesel fuel	++
	Kerosene	++
	White spirit	++
Chlorinated solvents	Trichloroethylene	--
	Trichloroethane	-
	Perchloroethylene	--
	Methylene chloride	--
	Carbon tetrachloride	--
	Chloroform	-
Aromatic solvents	Benzene	+
	Toluene	-
	Xylene	+
Aliphatic solvents	Hexane	++
	Heptane	++
Fluorinated solvents	Trichlorofluoromethane	--
Ketones	Acetone	-
	Methyl ethyl ketone	-

++ : Excellent resistance (continuous exposure)
+ : Good resistance (long-term exposure)
- : Limited resistance (short-term exposure possible)
-- : Poor resistance (avoid exposure)

5. MAINTENANCE

Resistance to professional detergent and disinfectant solutions.



Ethyl-based liquid preparation with surfactant	++
Mild alkaline liquid preparation with surfactant	++
Strong alkaline liquid preparation with disinfectant properties	--
Alkaline surfactant preparation with amphoteric antibacterial agent	+
Phosphoric acid-based surfactant preparation with disinfectant properties	++
Concentrated alkaline liquid preparation with strong ionic surfactant detergent	-
Concentrated alkaline liquid preparation with EDTA complexing agent	-

6. EQUIPMENT

■ 6.1 Cable entry plates and blanking plates

The enclosures are supplied with blanking plates

-  Functional plate
-  Blanking plate, depth 125 mm
-  Blanking plate, depth 200 mm

		Enclosure width (mm)					
		400	600	800	1000	1200	1600
		Plate width (mm)					
		224	424	624	824	2 x 424	2 x 624
Enclosure depth (mm)	400						
	500						
	600						
	800	x					x
	1000	x					x
	1200	x				x	x

IP43 sealing brush plates

Composed of 2 plates with sealing brushes

Cat.Nos	For enclosure width(mm)	For enclosure depth (mm)
3PECB040	400	400/500/600
3PECB060	600	400/500/600/800/1000/1200
3PECB080	800	400/500/600/800/1000/1200
3PECB100	1000	400/500/600/800/1000/1200
3PECB060 x 2	1200	400/500/600/800/1000
3PECB080 x 2	1600	400/500/600

Foam gasket plates IP43

Consisting of 2 sealing foam gasket plates, 25 x 30 mm

Cat.Nos	For enclosure width(mm)	For enclosure depth (mm)
3PECM040	400	400/500/600
3PECM060	600	400/500/600/800/1000/1200
3PECM080	800	400/500/600/800/1000/1200
3PECM100	1000	400/500/600/800/1000/1200
3PECM060 x 2	1200	400/500/600/800/1000
3PECM080 x 2	1600	400/500/600

Cable gland plates IP55

Cat.Nos	For enclosure width(mm)	For enclosure depth (mm)
3PECD040	400	400/500/600
3PECD060	600	400/500/600/800/1000/1200
3PECD080	800	400/500/600/800/1000/1200
3PECD100	1000	400/500/600/800/1000/1200
3PECD060 x 2	1200	400/500/600/800/1000
3PECD080 x 2	1600	400/500/600

6. EQUIPMENT (continued)

■ 6.1 Cable entry plates and blanking plates (continued)

Cabstop IP55 cable entry plates

Cable entries consisting of a clamping jaw for mechanical retention and elastomer zones for sealing.

Equipped with Cabstop plates 0 364 94/95/97.

Entry Ø 5 to 14 equivalent to PE ISO 16/20 and PE PG 9/11/13/16.

Entry Ø 14 to 24 equivalent to PE ISO 25/32 and PE PG 21/22.

Can be pierced directly with the cable (no tools required).


Supplied with sealing plugs to close a pierced entry while maintaining IP55, and cable release tools.

Cat.Nos	For enclosure width (mm)	For enclosure depth (mm)	Cabstop plates used
3PECS040	400	400/500/600	0 364 94
3PECS060	600	400/500/600/800 /1000/1200	0 364 96
3PECD080	800	400/500/600/800 /1000/1200	0 364 97
3PECD100	1000	400/500/600/800 /1000/1200	0 364 97
3PECD060 x 2	1200	400/500/600/800/1000	2 x 0 364 96
3PECD080 x 2	1600	400/500/600	2 x 0 364 97

■ 6.2 Bases and accessories


- Base to assemble: set of 4 feet, height 100 mm, Cat.No 3ZFRC + set of 2 plinths for installation on the enclosure width and set of 2 plinths for installation on the enclosure depth, Cat.No 3ZLIC...

3ZFRC + 3ZLIC040/050/060/080/100/120/160



When two enclosures are coupled, internal plinths (set of 2) Cat.No 3ZLIC... allow cable routing (pre-cut central section).

3ZLIC040/050/060/080/100




It is possible to stack two bases using kit Cat.No 3ZFRD

3ZFRD



■ 6.3 Plates

Partial plate Lina 12.5



Galvanized steel.

With pre-drilled holes allowing equipment installation without marking.

Automatic squaring:

- Ø 6,5 mm for insulating rivets


Cat.No 0 366 44 (trunking)

- Ø 3,3 mm for equipment with screws

Cat.No 0 347 45

Drilling for lifting.

Permissible load: 150 kg/m²





Cat.Nos	Height (mm)	For enclosure depth (mm)	Weight (kg)
3PMLIN080080	800	800	6,4
3PMLIN100080		1000	8
3PMLIN120080		1200	10
3PMLIN080100	1000	800	8
3PMLIN100100		1000	10,3
3PMLIN120100		1200	12,5

Partial plate Lina 25

Zinc-plated steel

Permissible load: 50 kg/m².



Cat.Nos	Height (mm)	For enclosure depth (mm)	Weight (kg)
3PMLAN060080	800	600	3,5
3PMLAN080080		800	4,6
3PMLAN100080		1000	6
3PMLAN120080		1200	7
3PMLAN160080	1000	1600	9,3
3PMLAN060100		600	4,3
3PMLAN080100		800	5,5
3PMLAN100100		1000	7
3PMLAN120100	1200	1200	8,3
3PMLAN160100		1600	11
3PMLAN060120		600	5
3PMLAN080120		800	6,7

Note: For enclosure with a height of 1200 mm, the partial plate used covers the full height of the enclosure

Reinforcement bracket Cat.No 3PMFC

Metal bracket used to reinforce a plate (solid or perforated) in tall enclosures. It adds a central fixing point to reduce plate deflection.

Galvanized steel


Set of 2

6. EQUIPMENT (continued)

■ 6.3 Plates (continued)

Plates for front insertion

Premarked with pitch 10 mm.
Drilling for lifting.
Permissible load: 200 kg/m².
Galvanized steel.
Mounting at different depths using
2 supports in galvanized steel
Cat.No 3SPM...




Cat.Nos	Height (mm)	For enclosure width (mm)	Weight (kg)
3PMF060120	1200	600	13,9
3PMF080120		800	18,3
3PMF060160	1600	600	18,6
3PMF080160		800	24,6
3PMF100160		1000	30,5
3PMF120160		1200	36,5
3PMF040180	1800	400	14,2
3PMF060180		600	20,9
3PMF080180		800	27,7
3PMF100180		1000	34,5
3PMF120180		1200	41,2
3PMF160180		1600 ⁽¹⁾	30,1
3PMF040200	2000	400	15,7
3PMF060200		600	23,3
3PMF080200		800	30,8
3PMF100200		1000	38,4
3PMF120200		1200	45,9
3PMF160200		1600 ⁽¹⁾	33,5
3PMF040220	2200	400	17,3
3PMF060220		600	25,6
3PMF080220		800	34,0
3PMF100220		1000	42,3
3PMF120220		1200	50,6
3PMF160220		1600 ⁽¹⁾	36,8

⁽¹⁾ : The plate for enclosure width 1600mm consists of 2 plates width 800mm. Junction kit is supplied.

Mounting plate supports


Set of 2

Cat.Nos	For enclosure depth (mm)	Weight (kg)
3SPM040	400	0,7
3SPM050	500	1,0
3SPM060	600	1,3
3SPM080	800	1,8
3SPM100	1000	2,3



Full width plain plates

The plate's useable surface area is equal to the width of the enclosure and ensures continuous connection between 2 extended enclosure plates.
Mounted via the front face of the enclosure.
Premarked with pitch 10 mm.
Drilling for lifting.
Permissible load: 200 kg/m².
Galvanized steel.
Cannot be used with 300 mm deep one-piece enclosures.



Cat.Nos	Height (mm)	For enclosure depth (mm)	Weight (kg)
3PMLT080160	1600	800	27,5
3PMLT060180	1800	600	24,2
3PMLT080180	1800	800	31,0
3PMLT100180	1800	1000	37,7
3PMLT120180	1800	1200	44,5
3PMLT060200	2000	600	27,0
3PMLT080200	2000	800	34,5
3PMLT100200	2000	1000	42,0
3PMLT120200	2000	1200	49,6

Compensation plates


Provides unbroken connection between 2 plain plates or Lina 12,5 plates.

For extendable enclosures.

Lina 12,5 perforation.

Galvanized steel.

Cat.Nos	For enclosure height (mm)	Weight (kg)
3PMC120	1200	3,0
3PMC160	1600	4,0
3PMC180	1800	4,6
3PMC200	2000	5,1
3PMC220	2200	5,7



Lina 12.5 plate

Galvanized steel.

With pre-drilled holes allowing equipment installation without marking.

Automatic squaring:

- Ø 6,5 mm for insulating rivets

Cat.No 0 366 44 (trunking)

- Ø 3,3 mm for equipment with screws

Cat.No 0 347 45


Drilling for lifting.

Permissible load: 150 kg/m²

Mounting at different depths using

2 supports in galvanized steel

Cat.No 3SPM...



Cat.Nos	Height (mm)	For enclosure width (mm)	Weight (kg)
3PMLIN080160	1600	800	23,8
3PMLIN120160		1200	35,8
3PMLIN060180	1800	600	20,2
3PMLIN080180		800	27,0
3PMLIN100180		1000	33,7
3PMLIN120180		1200	40,5
3PMLIN160180	2000	1600 ⁽¹⁾	29,6
3PMLIN060200		600	22,6
3PMLIN080200	2000	800	30,1
3PMLIN100200		1000	37,6
3PMLIN120200		1200	45,2
3PMLIN160200		1600 ⁽¹⁾	33,0


⁽¹⁾ : The plate for enclosure width 1600mm consists of 2 plates width 800mm. Junction kit is supplied.

6. EQUIPMENT (continued)

■ **6.3 Plates (continued)**

Lateral plates

Galvanized steel.
Mounting using 2 sliding supports supplied.
coulissants fournis.
Premarked with pitch 10mm.
Drilling for lifting.
Permissible load: 200 kg/m².



Cat.Nos	Height (mm)	For enclosure width (mm)	Weight (kg)
3PML060180	1800	600	26,7
3PML080180		800	33,6
3PML100180		1000	40,7
3PML120180		1200	47,7
3PML160180		1600 ⁽¹⁾	66,1
3PML060200	2000	600	29,4
3PML080200		800	37,2
3PML100200		1000	45,0
3PML120200		1200	52,9
3PML160200		1600 ⁽¹⁾	73,2
3PML060220	2200	600	32,2
3PML080220		800	40,8
3PML100220		1000	49,4
3PML120220		1200	58,0
3PML160220		1600 ⁽¹⁾	80,4

⁽¹⁾ : The plate for enclosure width 1600mm consists of 2 plates width 800mm. Junction kit is supplied.

■ **6.4 Cable fastening crossba**

Set of 2 – Galvanized steel
Allow the creation of partial frames in modular enclosures
Pre-positioning by hooking before final screw fastening.
For multifunction bars: perforations for nut clips at 25 mm pitch

Cat.Nos	For enclosure width or depth (mm)
3TRC040	400
3TRC050	500
3TRC060	600
3TRC080	800
3TRC100	1000


Possible uses detailed in the instructions:

- Bracing bar for depth
- In combination with Cat.No 3PMFC to maintain the rigidity of the solid plate
- Rail support for terminal block with Cat.No 3DINR060/070/080

■ **6.5 Enclosure assembly kit**

External assembly Cat.No 3KJLATE


Assembly set consisting of:
- 6 assembly components (right + left)
- 6 retaining shafts
- fasteners



Inner assembly Cat. No 3KJLATI

Assembly set consisting of:


- 4 brackets
- 2 coupling brackets
- nut clips
- fasteners





■ **6.6 Lifting**

Lifting rings Cat.No 3KLIFTA

Set of 4 lifting rings






Permissible load: 1000 kg




Lifting angles Cat.No 3KLIFTB

Set of 2

Balances the load between 2 enclosures during lifting.



Permissible load when 2 enclosures are joined: 930 kg




Permissible load when 3 enclosures are joined: 1400 kg

7. ACCESSORIES

■ **7.1 Tilting table Cat.No 3P47707**

600 mm metal shelf mounted on the enclosure door.

Compatible with all door widths by adding horizontal profiles if required.
RAL 7012




3 possible positions: vertical, horizontal, or inclined

Door width (mm)	Mounting method	Cat.Nos
600	Directly on cable duct doors	None
800	On horizontal profile	3P47720
1000	On horizontal profile	3P47721

7. ACCESSORIES (continued)

■ 7.2 Metal plan holder
RAL 7012



Cat.Nos	Mounting	For doors (width mm)	Internal dimensions (mm)		
			H	W	D
3P47645	Cable duct doors and adhesive	600 / 800 / 1000	275	400	50
3P47646	Cable duct doors	600		420	100
3P47647	Cable duct doors	800		620	100
3P47648	Cable duct doors	1000		820	100

■ 7.3 Door crosspieces / Angle brackets
Profiles for door accessories


The door crosspieces allow various accessories to be mounted inside the enclosure door.

Horizontal or vertical installation

They allow you to :

- secure cables with ties,
- mount cable ducts,
- support a writing shelf on 800 mm and 1000 mm doors
- mount DIN rails

Galvanized steel



Cat.Nos	For enclosure width (mm)
3P47719	600
3P47720	800
3P47721	1000

Angle bracket Cat.No 3P47718

Metal angle bracket designed to mount a DIN rail on the doors of an electrical enclosure. It slides onto the ends of the rails, ensuring quick fastening without drilling.

Mounting on cable duct doors.

Zinc-plated steel



■ 7.4 Door windows

IP 54


Anodized aluminum frame, opening angle 175° ± 5°

Polycarbonate window, 3 mm thick. Neoprene gasket.

Key lock No. 455

Supplied with drilling template

Protects devices, prevents accidental operations, and allows front panel visibility of equipment.



Cat.Nos	External dimensions (mm)			Viewing window dimensions (mm)		Usable depth (mm)
	H	W	D	H	W	
3P47545	300	400	50	230	330	42
3P47546	400	400	50	330	330	42
3P47547	500	500	50	430	430	42
3P47548	600	400	50	530	330	42
3P47549	600	600	50	630	530	42

■ 7.5 Door stop Cat.No 3P47302


Direct mounting on the enclosure frame

Door stop at end of travel (max. 115°)

Left or right installation

Locking possible at 90° or 115°

Galvanized steel




■ 7.6 Door contact Cat.No 3P47628

Mechanical contactor for

detecting the opening/closing of a enclosure door. Allows activation of a light or alarm when the door is opened.

Screw mounting, contact activated by pressure from the door.



■ 7.7 Cable clamping profiles and stainless steel clamp

For clamping cables with clamp Cat.No 0 347 38


Direct mounting on uprights, plates, or the frame of modular enclosures

Supplied with mounting device


Cable clamping diameter: 10 ≤ Ø ≤ 35 mm

Cat.Nos	For enclosure width (mm)
3P47235	600
3P47236	800
3P47237	1000
3P47238	1200
3P47239	1600

■ 7.8 Set of 2 supports for heavy loads



	L1 (mm)	L2 (mm)
3P47235	600	475
3P47236	800	675
3P47237	1000	875
3P47238	1200	1075
3P47239	1600	1475




3P47235	600	475	550
3P47236	800	675	750
3P47237	1000	875	950
3P47238	1200	1075	1150
3P47239	1600	1475	1550

Mount at the bottom of the enclosure, on support Cat.No 3SPM...

Adjustable mounting for equipment.

Supplied with M6, M8, M10 fixing devices.



Cat.Nos	For enclosure width (mm)	Maximum load (kg)
3P47475	600	300
3P47476	800	
3P47477	1000	

7. ACCESSORIES (continued)

■ 7.9 Roof extension Cat.No 3P47373


Roof extension for natural top ventilation
Height : 12 mm
IP 12B



Does not allow lifting.

■ 7.10 Wall mounting bracket Cat.No 3P47702

Direct mounting on the enclosure.
Accessories for wall mounting not supplied.
Stainless steel
Dimensions : 100 x 90 x 90 mm thickness 3 mm
Slot 20 x 16 mm



8. 19" ACCESSORIES

■ 8.1 19" uprights

Set of 2
Load per U: 10 kg
Square perforation: 9,5 x 9,5 mm
Galvanized steel upright, with U marking
Depth adjustable in 25 mm increments
Mount on support Cat.No 3SPM... for 800 mm width



Cat.Nos	For enclosure (mm)	Number of U
3P48218	Height 1800 Width 600/800	38
3P48220	Height 2000 Width 600/800	42
3P48222	Height 2200 Width 600/800	47

9. STANDARDS AND REGULATIONS

Compliant with regulations for public-access buildings and workplaces

RoHS

Compliance with the 2011/65/EU Directive (RoHS), as modified by the 2015/863/EU Delegated Directive, on the restriction of the use of certain hazardous substances in electrical and electronic equipment


REACH

The substances identified as SVHC (Substances of Very High Concern) according to the REACH Regulation (1907/2006), if present in the products at a concentration above 0.1% weight by weight, are declared inside the European SCIP database. At the date of publication of this document none of the substance listed in the annex XIV is found in this product.

Packaging

Design and manufacture of packaging compliant with European Directive 94/62/CE.

10. OTHER INFORMATION



Instruction sheet : detailed mounting procedures, available on e-catalog

Workshop manual : mounting information, equipment, accessories and other information available on e-catalog

PEP : available on e-catalog

XLPro4 Calcul : Calculation notes creation software, addressed to installers, design office and maintenance operators. Definition of the electrical characteristics of a low voltage installation in compliance with the applicable standards.

XLPro4 Panels : Distribution panel design software, addressed to panelbuilders and electrical panel designers. Design of the electrical distribution of the panel, production of electrical diagrams, establishment of products and overall costing of the project.