


Arteor™ Advance Control for Hotel equipment

Cat. No(s): AC22112MW/MB/MT/CH/DB/RS




1. USE

Master switch lighting controls mechanisms for hotel.
Mechanisms supplied with cover.
To be equipped with support frame and plate.
Flush-mounting or surface-mounting.

2. RANGE

Designation	Finishes					
	Matt White	Matt Black	Matt Titanium	Chapagne	Dark Bronze	Rose
2 modules 2-way 20AX all lights ON/OFF master switch	AC22112MW	AC22112MB	AC22112MT	AC22112CH	AC22112DB	AC22112RS

3. DIMENSIONS (mm)



Cat. Nos	A	B	C
AC22112MW/MB/MT/CH/DB/RS	45.05	45.05	40.1

4. CONNECTION

Type of terminals: with screws
Terminal capacity: 2 x 2.5 mm² or 1 x 1.5 mm²
Stripping length: 10 mm

5. TECHNICAL CHARACTERISTICS

■ 5.1 Mechanical characteristics


Impact test: IK 04
Protection against solid bodies and liquids: IP 40 (mounted)
IP 20 (alone)

■ 5.2 Material characteristics

Rocker: PC
Mechanism: PC
Self-extinguishing:
850°C/30 s for insulating parts holding live parts in place.
650°C/30 s for other parts made of insulating materials.

■ 5.3 Electrical characteristics

Voltage: 250 V~
Current: 20 AX
Maximum power on lamps with integrated ballast
(LED lamps and compact fluorescent): 250 W



■ 5.4 Climate characteristics

Storage temperature: - 10° c to + 70° C
Usage temperature: - 5° C to + 35° C

6. CLEANING

Surface cleaning with a cloth.
Do not use: acetone, tar remover, trichloroethylene.
Resistance to the following agents: Hexane, Methylated spirits, Soapy water, diluted ammonia, diluted pure bleach 10%, Glass cleaning substance, Pre-impregnated wipes.

Caution: Always test before using other special cleaning products.

7. STANDARDS AND APPROVALS

Conforme to IEC 60669-1 Standard.
Compliance with installation and manufacturing standards.
Refer to e-catalogue.