



Arteor™ Advance Control for Hotel equipment

Cat. No(s): AA23115MW/MB/MT - AC23115MW/MB/MT




1. USE

Master push lighting controls mechanisms for hotel.
Mechanisms supplied with cover.
To be equipped with support frame and plate.
Flush-mounting or surface-mounting.

2. RANGE

Designation	Finishes		
	Matt White	Matt Black	Matt Titanium
1 module 2-way master push button	AA23115MW	AA23115MB	AA23115MT
2 modules 2-way master push button	AC23115MW	AC23115MB	AC23115MT

3. DIMENSIONS (mm)



Cat. Nos	A	B	C
AA23115MW/MB/MT	61.8	22.5	41.06
AC23115MW/MB/MT	45.05	45.05	38.06

4. CONNECTION

Type of terminals: with screws
Terminal capacity: 2 x 2.5 mm² or 1 x 1.5 mm²
Stripping length: 10 mm

5. TECHNICAL CHARACTERISTICS

- 5.1 Mechanical characteristics
Impact test: IK 04
Protection against solid bodies and liquids: IP 40 (mounted)
IP 20 (alone)
- 5.2 Material characteristics
Rocker: PC
Mechanism: PC
Self-extinguishing:
850°C/30 s for insulating parts holding live parts in place.
650°C/30 s for other parts made of insulating materials.
- 5.3 Electrical characteristics
Voltage: 250 V~
Current: 10 A
- 5.4 Climate characteristics
Storage temperature: - 10° c to + 70° C
Usage temperature: - 5° C to + 35° C

6. CLEANING

Surface cleaning with a cloth.
Do not use: acetone, tar remover, trichloroethylene.
Resistance to the following agents: Hexane, Methylated spirits, Soapy water, diluted ammonia, diluted pure bleach 10%, Glass cleaning substance, Pre-impregnated wipes.

Caution: Always test before using other special cleaning products.

7. STANDARDS AND APPROVALS

Conforme to IEC 60669-1 Standard.
Compliance with installation and manufacturing standards.
Refer to e-catalogue.