



## Arteor™ Advance Control for Hotel equipment

Cat. No(s): AA21117MW/MB/MT - AC21117MW/MB/MT  
AA23119MW/MB/MT - AC23119MW/MB/MT




### 1. USE

Bed lights controls mechanisms for hotel.  
Mechanisms supplied with cover.  
To be equipped with support frame and plate.  
Flush-mounting or surface-mounting.

### 2. RANGE

| Designation                                  | Finishes   |            |               |
|----------------------------------------------|------------|------------|---------------|
|                                              | Matt White | Matt Black | Matt Titanium |
| 2x1 module slender switch for bedlights 10AX | AA21117MW  | AA21117MB  | AA21117MT     |
| 2x1 module square switch for bedlights 10AX  | AC21117MW  | AC21117MB  | AC21117MT     |
| 2x1 module slender push for bedlights 10A    | AA23119MW  | AA23119MB  | AA23119MT     |
| 2x1 module square push for bedlights 10A     | AC23119MW  | AC23119MB  | AC23119MT     |

3. DIMENSIONS (mm)



| Cat. Nos                           | A     | B     | C     |
|------------------------------------|-------|-------|-------|
| AA21117MW/MB/MT<br>AA23119MW/MB/MT | 61.8  | 45    | 41.06 |
| AC21117MW/MB/MT<br>AC23119MW/MB/MT | 45.05 | 45.05 | 38.06 |

4. CONNECTION

Type of terminals: with screws  
Terminal capacity: 2 x 2.5 mm<sup>2</sup> or 1 x 1.5 mm<sup>2</sup>  
Stripping length: 10 mm

5. TECHNICAL CHARACTERISTICS

■ 5.1 Mechanical characteristics


Impact test: IK 04  
Protection against solid bodies and liquids: IP 40 (mounted)  
IP 20 (alone)

■ 5.2 Material characteristics

Rocker: PC  
Mechanism: PC  
Self-extinguishing:  
850°C/30 s for insulating parts holding live parts in place.  
650°C/30 s for other parts made of insulating materials.

■ 5.3 Electrical characteristics

Voltage: 250 V~  
Current: \_ 10 AX for AA21117MW/MB/MT  
AC21117MW/MB/MT  
Maximum power on lamps with integrated ballast  
(LED lamps and compact fluorescent): 100 W  
\_ 10 A for AA23119MW/MB/MT  
AC23119MW/MB/MT



■ 5.4 Climate characteristics

Storage temperature: - 10° c to + 70° C  
Usage temperature: - 5° C to + 35° C

6. CLEANING

Surface cleaning with a cloth.  
Do not use: acetone, tar remover, trichloroethylene.  
Resistance to the following agents: Hexane, Methylated spirits, Soapy water, diluted ammonia, diluted pure bleach 10%, Glass cleaning substance, Pre-impregnated wipes.

**Caution:** Always test before using other special cleaning products.

7. STANDARDS AND APPROVALS

Conforme to IEC 60669-1 Standard.  
Compliance with installation and manufacturing standards.  
Refer to e-catalogue.