


Arteor™ Advance Blanking plates Italian/US standard Classic Collection

Cat. No(s): AC1503MW/MB/MT




1. USE

Blanking plate to be equipped with frame.

2. RANGE

Designation	Finishes		
Classic Collection	Matt White	Matt Black	Matt Titanium
<i>Blanking cover plates for Italian/US standard</i>			
2X4 Italian/US blanking plate	AC1503MW	AC1503MB	AC1503MT

3. DIMENSIONS (mm)



Cat. Nos	A	B	C
AC1503MW/MB/MT	90	127	8.5

4. TECHNICAL CHARACTERISTICS

■ 4.1 Mechanical characteristics

Protection against impacts: IK 04

Protection against solid bodies and/or liquids: IP 20

■ 4.2 Material characteristics

Plate: PC

Halogen-free

UV-resistant

■ 4.3 Climate characteristics

Storage temperature: - 10° c to + 70° C

Usage temperature: - 5° C to + 35° C

5. CLEANING

Surface cleaning with a cloth.

Do not use: acetone, tar remover, trichloroethylene.

Resistance to the following agents: Hexane.

Methylated spirits, Soapy water, diluted ammonia, diluted pure bleach 10%, Glass cleaning substance, Pre-impregnated wipes.

Caution: Always test before using other special cleaning products.

6. STANDARDS AND APPROVALS

Compliance with installation and manufacturing standards.

Refer to e-catalogue.