


Arteor™ Advance USB Type C+C charger - 15 W

Cat. No(s): AC3412MW/MB/MT/DB/CH/RS




1. USE

For recharging portable devices such as phones, smartphones, MP3 or MP4, loudspeakers, watches, game consoles, powerbanks.
Exclusive mounting on tertiary supports.
For installation in floor boxes, columns, mini-columns, desktop multi-outlet extensions and DLP trunkings.
Not compatible with Batibox flush-mounting boxes.

2. RANGE

15 W USB charger	Matt White	Matt Black	Matt Titanium
USB Type-C+C charger 1 module	AC3412MW	AC3412MB	AC3412MT
	Chapagne	Dark Bronze	Rose
	AC3412CH	AC3412DB	AC3412RS

3. DIMENSIONS (mm)



A	B	C	D
45	22.5	41	8.5

4. CONNECTION

Type of terminals: with screws
Terminal capacity: 1 x 2.5 mm² - 2 x 1.5 mm²
Stripping length: 6 mm
Screwdriver: flat 3.5 mm
Circuit Breaker: MAX. 16 A

Necessary safety precautions:



**Switch OFF the power at the main circuit breaker.
Make sure that the power is OFF before continuing
with the installation.**

5. TECHNICAL CHARACTERISTICS

■ 5.1 Mechanical characteristics

Impact tests: IK 04
Penetration by solid bodies and liquids: IP 40

■ 5.2 Material characteristics

Base: PC V-0 class
Cover: painted PC V-0 class

Self-extinguishing:
850°C/30 s for insulating components holding live parts in place.
650°C/30 s for other insulating components.

■ 5.3 Electrical characteristics

All values listed below are measured at an ambient temperature of + 20° and after 30 minutes of operation.

Nominal input voltage	100-240 V~
Nominal input frequency	50/60 Hz
Nominal input current	0.5 A
Max. nominal output current	3.0 A
Max. output power	15 W
Nominal output voltage	5.0 V=
Average efficiency in active mode	85 %
Stand-by power consumption	< 0.1 W
Consumption class without load and average level of efficiency: Level VI	
Protection class	II - Low voltage

*Note: European Standard (CE) No. 278/2009-6 April 2009, directive 2009/125/CE relating to ecodesign requirements for AC/DC power supplies.

Note: To optimize the charging time of your device, ensure turn it off during the charging phase.

■ 5.4 Climate characteristics

Storage temperature: -20°C to +70°C
Operating temperature: +5°C to +40°C

6. CLEANING

Surface cleaning with a cloth.

Do not use: acetone, tar remover, trichloroethylene.

Resistance to the following agents: Hexane,

Methylated spirits, Soapy water, diluted ammonia, diluted pure bleach

10%, Glass cleaning substance, Pre-impregnated wipes.

Caution: Always test before using other special cleaning products.

7. STANDARDS AND APPROVALS

Compliant with installation and manufacturing standards.

See e.catalogue