


Arteor™ Advance with Netatmo Plate British Standard Classic Collection

Cat. No(s): AC1112MW/MB/MT/CH/DB/RS



1. USE

Finishing plates.


The plates clip into notches on screw and/or claw fixings.

Protection film must be removed only once site work is fully completed.

2. RANGE

Designation	Finishes					
Classic Collection	Matt White	Matt Black	Matt Titanium	Champagne	Dark Bronze	Rose
Square Version						
2 x 3 modules british standard plate for IOT socket- 2 gang	AC1112MW	AC1112MB	AC1112MT	AC1112CH	AC1112DB	AC1112RS

3. DIMENSIONS (mm)



Cat. Nos	A	B	C
AC1112MW/MB/MT/CH/DB/RS	90	127	8

4. TECHNICAL CHARACTERISTICS

■ 4.1 Mechanical characteristics

Protection against impacts: IK 04

Protection against solid bodies and/or liquids: IP 20

■ 4.2 Material characteristics

Adjuster : PC

Plate: PC

Self-extinguishing: 650°C/30 s

Halogen-free

UV-resistant

■ 4.3 Climate characteristics

Storage temperature: - 10° c to + 70° C

Usage temperature: - 5° C to + 35° C

5. CLEANING

Surface cleaning with a cloth.

Do not use: acetone, tar remover, trichloroethylene.

Resistance to the following agents: Hexane.

Methylated spirits, Soapy water, diluted ammonia, diluted pure bleach 10%, Glass cleaning substance, Pre-impregnated wipes.

Caution: Always test before using other special cleaning products.

6. STANDARDS AND APPROVALS

Compliance with installation and manufacturing standards.

Refer to e-catalogue.