


Connected indoor temperature and humidity sensor

Cat. No(s) : 069060




1. USE

Measures indoor temperature and humidity. Enables automated scenarios. The collected data is displayed in the Home + Control app, where it can be used to create automations, trigger alerts, or send notifications based on user-defined thresholds.

2. RANGE

Description	Reference
Must be associated with a Legrand "with Netatmo" connected gateway. Supplied with battery.	069060

3. DIMENSIONS (mm)



A	B
60	16.5

4. FONCTIONNEMENT

Measurement thresholds

Temperature range: 0°C to +50°C

Temperature range: 0°C to +50°C

Range: 180 m

Installation height: < 2 m

5. TECHNICAL CHARACTERISTICS

■ 5.1 Mechanical characteristics

Impact resistance: IK04

Protection against solid objects/liquids: IP20

■ 5.2 Material characteristics

ABS

UV resistant

■ 5.3 Electrical characteristics

Battery: CR2450 - 3V

Frequency : 2,4 GHz to 4,4835 GHz

Power level < 100mW

■ 5.4 Climatic characteristics

Storage temperature: 0°C to +45°C

Recommended installation temperature: +5°C to +35°C

6. CARE

Surface cleaning with a cloth.

Do not use: acetone, tar remover, trichloroethylene.

Resistance to the following agents:

Hexane, methylated spirits, soapy water, diluted ammonia, pure bleach diluted to 10%, window-cleaning products, pre-impregnated wipes.

Caution: Always test before using other special cleaning products



Take care to recycle the battery appropriately.

7. STANDARDS AND APPROVALS

Complies with international standards relating to electrical safety and the use of radio frequencies.

The undersigned, LEGRAND, declares that the radio-electric equipment type (0 690 60) complies with directive 2014/53/EU.

The full text of the EU declaration of conformity is available on the following website: www.legrand.com/ecatalogue