










In(A)				Icw (kA)									
IP ≤ 30	IP > 30			15	20	25	30	35	40	45	50	60	70
800	630	1 x 91887 AL	91886 SLAL	1600	1000	800	700	600	600	500	500	--	--
			91888 SLAL	1600	1000	800	600	500	500	400	400	--	--
1000	800	1 x 91888 AL	91886 SLAL	1600	1000	800	700	600	600	500	500	--	--
			91888 SLAL	1600	1000	800	600	500	500	400	400	--	--
1250	1000	1 x 91889 AL	91886 SLAL	1600	1000	800	700	600	600	500	500	500	400
			91888 SLAL	1600	1000	800	600	500	500	400	400	400	300
1450	1250	1 x 91891 AL	91886 SLAL	1600	1000	800	700	600	600	500	500	500	400
			91888 SLAL	1600	1000	800	600	500	500	400	400	400	300
1750	1600	1 x 91883 AL	91886 SLAL	1600	1000	800	700	600	600	500	500	500	400
			91888 SLAL	1600	1000	800	600	500	500	400	400	400	300
3500	3200	2 x 91883 AL ^(A) (B)	2 x 91886 SLAL	1600	1000	800	700	600	600	500	500	500	400
			2 x 91888 SLAL	1600	1000	800	600	500	500	400	400	400	300





(A)  91833 ALP1
91833 ALP2







L	A	B
350	91886 SLAL	
600	91886 SLAL + 81825	91888 SLAL
850	91886 SLAL + 81825/10	91888 SLAL + 81825/10







A




B



M6 : 10/15 Nm





P	(A)	(B)
600	91886 SLAL	
850	91886 SLAL + 81825	91888 SLAL + 81825/10

