



FASCLIC AUTO PG

Reference(s) : 082 060/070/080/090, 082 100/200/250/300/400.



RANGE.




Ref	Code	Poids (kg/ml)	Weight (lb/ft)	L (mm)	L (inch)
FCFA 54/50PG	082060	0,677	0,455	50	1,97
FCFA 54/100PG	082070	0,763	0,513	100	3,94
FCFA 54/150PG	082080	1,019	0,685	150	5,91
FCFA 54/200PG	082090	1,326	0,891	200	7,88
FCFA 54/300PG	082100	2,006	1,348	300	11,82
FCFA 54/400PG	082200	3,149	2,116	400	15,76
FCFA 54/450PG	082250	3,259	2,190	450	17,73
FCFA 54/500PG	082300	3,559	2,392	500	19,7
FCFA 54/600PG	082400	4,016	2,699	600	23,64


Ref	Matière Raw material	Norme Standard	Finition Coating	Norme Standard
COUPLER FASCLIC AUTO	DC01 C390	EN 10139	Fe/Zn 12/A	EN ISO 2081
BOTTOM PLATE	DC01 Am	EN 10130	Fe/Zn 12/A	EN ISO 2081

RANGE.


Width 50 to 200, coupler Fasclic auto alone.




Width 300, coupler Fasclic auto + 1 bottom plate




Width 400 to 500, coupler Fasclic auto + 2 bottom plates.



Width 600, coupler Fasclic auto + 3 bottom plates.



Bottom plate



To prepare the bottom plate before fixing:



Note :

From width 50 to 200 = minimum distance to the wall 10mm
From width 300 to 600 = minimum distance to the wall 13mm

