



Arteor™ Advance Plates German/French standard Statement Collection

Cat. No(s): AC1120NB/SA - AC1121NB/SA - AC1122NB/SA
AC1123NB/SA - AC1133NB/SA



AC1120NB/SA



AC1133NB/SA


1. USE

Finishing plates.
The plates clip into notches on screw and/or claw fixings.
Protection film must be removed only once site work is fully completed.

2. RANGE

Designation Statement Collection	Finishes	
	Midnight Blue	Solid Aluminium
Square Version		
1 module german/french standard plate	AC1120NB	AC1120SA
2 modules german/french standard plate	AC1121NB	AC1121SA
2x6 modules german/french standard plate	AC1122NB	AC1122SA
3x2 modules german/french standard horizontal plate	AC1123NB	AC1123SA
2x2 modules german/french standard horizontal plate	AC1133NB	AC1133SA

3. DIMENSIONS (mm)



Cat. Nos	A	B	C
AC1120NB/SA AC1121NB/SA	90	90	8.5
AC1133NB/SA	90	157	8.5
AC1123NB/SA	90	237.5	8.5
AC1122NB/SA	178	237.5	8.5

4. TECHNICAL CHARACTERISTICS

■ **4.1 Mechanical characteristics**

Impact test: IK 02

■ **4.2 Material characteristics**

Ajuster: PC

Plate: Metal

Self-extinguishing: 650°C/30 s

■ **4.3 Climate characteristics**

Storage temperature: - 10° c to + 70° C

Usage temperature: - 5° C to + 35° C

5. CLEANING

Surface cleaning with a cloth.

Do not use: acetone, tar remover, trichloroethylene.

Resistance to the following agents: Hexane.

Methylated spirits, Soapy water, diluted ammonia, diluted pure bleach
10%, Glass cleaning substance, Pre-impregnated wipes.

Caution: Always test before using other special cleaning products.

6. STANDARDS AND APPROVALS

Compliance with installation and manufacturing standards.

Refer to e-catalogue.