


Connected indoor temperature and humidity sensor




1. USE

This sensor measures the temperature and humidity inside a room. The collected data appears in the Home + Control app, where it can be used to create automations, trigger alerts, or send notifications based on thresholds set by the user.

2. RANGE

Must be paired with a Legrand "with Netatmo" connected gateway. To be equipped with a cover plate.

3. DIMENSIONS (mm)



A	B	C
73	76	12

4. CONNECTION

Measurement thresholds

Temperature range: 0° C à + 50° C
Humidity range: 0 à 100%
Range: 180 meters in open field
Maximum operating height: <2 m

5. TECHNICAL CHARACTERISTICS

■ 5.1 Mechanical characteristics

Protection against impacts: IK 04
Protection against: IP 20

■ 5.2 Material characteristics

ABS and PC
UV-resistant

■ 5.3 Electrical characteristics

Battery: CR2450 - 3 V
Frequency bands: 2,4 GHz à 2,4835 GHz
Power level: < 100 mW

■ 5.4 Climate characteristics

Storage temperature: 0° C à 45° C
Recommended installation temperatures : +5° C à + 35° C

6. CARE

Wipe the surface clean with a cloth.
Do not use: acetone, tar remover, or trichloroethylene.

Resistant to the following products: hexane, rubbing alcohol, soapy water, diluted ammonia, undiluted bleach diluted to 10%, window cleaner, and pre-moistened wipes.

Caution : Before using specific cleaning products, a preliminary test is required.



Battery Recycling Precautions

7. STANDARDS AND APPROVALS

The undersigned, LEGRAND, declares that the radio-electric equipment type (K4587C) complies with directive 2014/53/EU. The full text of the EU declaration of conformity is available on the following website: www.legrand.com/ecatalogue

Lorem ipsum
 Lorem ipsum
 Lorem ipsum

Cat. No(s): X XXX XX - X XXX XX