

P31 - COUDE 45°
P31 - FLAT BEND 45°

 Référence(s) : **480960/61/62/63/64/65/66**
 Items(s) : **482960/61/62/63/64/65/66**




100 mm



100 -> 150 mm



200 -> 600 mm


1. GAMME/RANGE
P31 - COUDE 45D SLIDE-IN H100 GS
P31 - FLAT BEND 45D H100 PG

Designation Description	Code	Poids Weight (Kg)	Épaisseur Thickness (mm)	Matière Raw Material	Norme matière Standard Raw Material	Finition Coating	Norme Finition Standard Coating	Section (mm ²)
P31-COUE 45D SLIDE-IN 100X100 GS P31-FLAT BEND 45D 100X100 PG	480960	0,46	0,7	DX51D + Z200	EN 10346	GS/PG/Z	EN 10346	10231
P31-COUE 45D SLIDE-IN 100X150 GS P31-FLAT BEND 45D 100X150 PG	480961	0,50	0,7	DX51D + Z200	EN 10346	GS/PG/Z	EN 10346	15296
P31-COUE 45D SLIDE-IN 100X200 GS P31-FLAT BEND 90 100X200 PG	480962	0,62	0,7	DX51D + Z200	EN 10346	GS/PG/Z	EN 10346	20361
P31-COUE 45D SLIDE-IN 100X300 GS P31-FLAT BEND 45D 100X300 PG	480963	0,88	0,7	DX51D + Z200	EN 10346	GS/PG/Z	EN 10346	30491
P31-COUE 45D SLIDE-IN 100X400 GS P31-FLAT BEND 45D 100X400 PG	480964	1,18	0,7	DX51D + Z200	EN 10346	GS/PG/Z	EN 10346	40621
P31-COUE 45D SLIDE-IN 100X500 GS P31-FLAT BEND 45D 100X500 PG	480965	1,53	0,7	DX51D + Z200	EN 10346	GS/PG/Z	EN 10346	50751
P31-COUE 45D SLIDE-IN 100X600 GS P31-FLAT BEND 45D 100X600 PG	480966	1,92	0,7	DX51D + Z200	EN 10346	GS/PG/Z	EN 10346	60881

 Classe de résistance contre la corrosion 3 (IEC 61537)
 Corrosion resistance classification 3 (IEC 61537)




P31 - COUDE 45D SLIDE-IN H100 GC
P31 - FLAT BEND 45D H100 HDG

Designation Description	Code	Poids Weight (Kg)	Épaisseur Thickness (mm)	Matière Raw Material	Norme matière Standard Raw Material	Finition Coating	Norme Finition Standard Coating	Section (mm ²)
P31-COUE 45D SLIDE-IN 100X100 GC P31-FLAT BEND 45D 100X100 HDG	482960	0,51	0,7	DC01	EN 10130	GC/HDG/C	ISO 1461	10231
P31-COUE 45D SLIDE-IN 100X150 GC P31-FLAT BEND 45D 100X150 HDG	482961	0,55	0,7	DC01	EN 10130	GC/HDG/C	ISO 1461	15296
P31-COUE 45D SLIDE-IN 100X200 GC P31-FLAT BEND 45D 100X200 HDG	482962	0,68	0,7	DC01	EN 10130	GC/HDG/C	ISO 1461	20361
P31-COUE 45D SLIDE-IN 100X300 GC P31-FLAT BEND 90 100X300 HDG	482963	0,97	0,7	DC01	EN 10130	GC/HDG/C	ISO 1461	30491
P31-COUE 45D SLIDE-IN 100X400 GC P31-FLAT BEND 90 100X400 HDG	482964	1,30	0,7	DC01	EN 10130	GC/HDG/C	ISO 1461	40621
P31-COUE 45D SLIDE-IN 100X500 GC P31-FLAT BEND 45D 100X500 HDG	482965	1,68	0,7	DC01	EN 10130	GC/HDG/C	ISO 1461	50751
P31-COUE 45D SLIDE-IN 100X600 GC P31-FLAT BEND 45D 100X600 HDG	482966	2,11	0,7	DC01	EN 10130	GC/HDG/C	ISO 1461	60881

 Classe de résistance contre la corrosion 6 (IEC 61537)
 Corrosion resistance classification 6 (IEC 61537)

P31 - COUDE 45°
P31 - FLAT BEND 45°

Référence(s) : 481272/73/74/75/76/77/78
Items(s) : 483272/73/74/75/76/77/78



1. GAMME/RANGE

P31 - COUDE PERFORÉ 45D SLIDE-IN H100 GS
P31 - FLAT BEND 45D TRAY PERF H100 PG

Designation Description	Code	Poids Weight (Kg)	Épaisseur Thickness (mm)	Matière Raw Material	Norme matière Standard Raw Material	Finition Coating	Norme Finition Standard Coating	Section (mm ²)
P31-COUDE PERFORÉ 45D SLIDE-IN 100X100 GS P31-FLAT BEND 45D TRAY PERF 100X100 PG	481272	0,38	0,7	DX51D + Z200	EN 10346	GS/PG/Z	EN 10346	10231
P31-COUDE PERFORÉ 45D SLIDE-IN 100X150 GS P31-FLAT BEND 45D TRAY PERF 100X150 PG	481273	0,49	0,7	DX51D + Z200	EN 10346	GS/PG/Z	EN 10346	15296
P31-COUDE PERFORÉ 45D SLIDE-IN 100X200 GS P31-FLAT BEND 45D TRAY PERF 100X200 PG	481274	0,60	0,7	DX51D + Z200	EN 10346	GS/PG/Z	EN 10346	20361
P31-COUDE PERFORÉ 45D SLIDE-IN 100X300 GS P31-FLAT BEND 45D TRAY PERF 100X300 PG	481275	0,85	0,7	DX51D + Z200	EN 10346	GS/PG/Z	EN 10346	30491
P31-COUDE PERFORÉ 45D SLIDE-IN 100X400 GS P31-FLAT BEND 45D TRAY PERF 100X400 PG	481276	1,15	0,7	DX51D + Z200	EN 10346	GS/PG/Z	EN 10346	40621
P31-COUDE PERFORÉ 45D SLIDE-IN 100X500 GS P31-FLAT BEND 45D TRAY PERF 100X500 PG	481277	1,49	0,7	DX51D + Z200	EN 10346	GS/PG/Z	EN 10346	50751
P31-COUDE PERFORÉ 45D SLIDE-IN 100X600 GS P31-FLAT BEND 45D TRAY PERF 100X600 PG	481278	1,88	0,7	DX51D + Z200	EN 10346	GS/PG/Z	EN 10346	60881

Classe de résistance contre la corrosion 3 (IEC 61537)
Corrosion resistance classification 3 (IEC 61537)

P31 - COUDE PERFORÉ 45D SLIDE-IN H100 GC
P31 - FLAT BEND 45D TRAY PERF H100 HDG

Designation Description	Code	Poids Weight (Kg)	Épaisseur Thickness (mm)	Matière Raw Material	Norme matière Standard Raw Material	Finition Coating	Norme Finition Standard Coating	Section (mm ²)
P31-COUDE PERFORÉ 45D SLIDE-IN 100X100 GC P31-FLAT BEND 45D TRAY PERF 100X100 HDG	483272	0,42	0,7	DC01	EN 10130	GC/HDG/C	ISO 1461	10231
P31-COUDE PERFORÉ 45D SLIDE-IN 100X150 GC P31-FLAT BEND 45D TRAY PERF 100X150 HDG	483273	0,54	0,7	DC01	EN 10130	GC/HDG/C	ISO 1461	15296
P31-COUDE PERFORÉ 45D SLIDE-IN 100X200 GC P31-FLAT BEND 45D TRAY PERF 100X200 HDG	483274	0,66	0,7	DC01	EN 10130	GC/HDG/C	ISO 1461	20361
P31-COUDE PERFORÉ 45D SLIDE-IN 100X300 GC P31-FLAT BEND 45D TRAY PERF 100X300 HDG	483275	0,93	0,7	DC01	EN 10130	GC/HDG/C	ISO 1461	30491
P31-COUDE PERFORÉ 45D SLIDE-IN 100X400 GC P31-FLAT BEND 45D TRAY PERF 100X400 HDG	483276	1,26	0,7	DC01	EN 10130	GC/HDG/C	ISO 1461	40621
P31-COUDE PERFORÉ 45D SLIDE-IN 100X500 GC P31-FLAT BEND 45D TRAY PERF 100X500 HDG	483277	1,64	0,7	DC01	EN 10130	GC/HDG/C	ISO 1461	50751
P31-COUDE PERFORÉ 45D SLIDE-IN 100X600 GC P31-FLAT BEND 45D TRAY PERF 100X600 HDG	483278	2,07	0,7	DC01	EN 10130	GC/HDG/C	ISO 1461	60881


Classe de résistance contre la corrosion 6 (IEC 61537)
Corrosion resistance classification 6 (IEC 61537)

P31 - COUDE 45°
P31 - FLAT BEND 45°

Référence(s) : **480960/61/62/63/64/65/66**
Item(s) : **482960/61/62/63/64/65/66**
481272/73/74/75/76/77/78
483272/73/74/75/76/77/78


2. DIMENSIONS (mm)

Designation Description	Largeur Width (W mm)	Rayon Radius (mm)	L1 (mm)	L2 (mm)
P31-COUDE 45D SLIDE-IN 100x100 P31-FLAT BEND 45D 100X100	102,4	99,3	246,8	168,4
P31-COUDE 45D SLIDE-IN 100x150 P31-FLAT BEND 45D 100X150	152,4	99,3	285	168,4
P31-COUDE 45D SLIDE-IN 100x200 P31-FLAT BEND 45D 100X200	202,4	99,3	323,3	168,4
P31-COUDE 45D SLIDE-IN 100x300 P31-FLAT BEND 45D 100X300	302,4	99,3	399,8	168,4
P31-COUDE 45D SLIDE-IN 100x400 P31-FLAT BEND 45D 100X400	402,4	99,3	476,4	168,4
P31-COUDE 45D SLIDE-IN 100x500 P31-FLAT BEND 45D 100X500	502,4	99,3	552,9	168,4
P31-COUDE 45D SLIDE-IN 100x1000 P31-FLAT BEND 45D 100X1000	602,4	99,3	625,4	168,4





P31 - COUDE 45°
P31 - FLAT BEND 45°

Référence(s) : 480960/61/62/63/64/65/66
Item(s) : 482960/61/62/63/64/65/66
481272/73/74/75/76/77/78
483272/73/74/75/76/77/78



Référence(s) : 341895 (PG)
Item(s) : 346895 (AISI 316L)

3. INSTALLATION



Detail A

