


Power cable IEC 60320 C19 to IEC 60309 16A 2P+N+E

Catalogue number(s) : 6 469 05/06



1. USE

Power cord IEC 60320 C19 to IEC 60309 16A 2P+E plug.
 Rotary locking mechanism on C19 plug that fits any standard C20 inlet
 to avoid accidental disconnection.

2. DESCRIPTION

Cat number	Color	Length (m)
6 469 05	Black	1.5
6 469 06	Black	3

3. TECHNICAL SPECIFICATIONS

SPECIFICATION	DESCRIPTION
High potential test voltage	2000VAC (1min 50Hz)
Rating	TUV : 16A 250VAC
Operation temperature	-20°C - +70°C
Flammability corresponding to	Cable (H05VVF) : IEC60332-1. Cat F2
Conductor size	2.5 mm ²
Connector - End 1	C19 - IEC60320 1P+N+E with rotary locking mechanism Locking retention force : 100N
Connector - End 2	Plug IEC60309 16A 1P+N+E IP44 - IK09

4. STANDARDS AND APPROVALS

- IEC 60320-1
- IEC 60309

4.1 REGULATORY APPROVALS

CE, UKCA, CMIM
 RoHS directive (Restriction of Hazardous Substances)
 REACH regulations (Registration, Evaluation, Authorisation & restriction
 of Chemicals).