


USB Type-C charger - 20 W - Power Delivery**1. USE**

PC, tablets, smartphones.

Optimizes the charging speed of Power Delivery terminals.


USB Power Delivery is the new fast charging technology built into iOS/Apple and Android/Google devices.

Technology enabling a faster charging level than conventional technologies, operating via an exchange between the terminal and the charger.

2. RANGE

Designation	Item
20W USB charger TYPE C Power Delivery 1 module	<input type="checkbox"/> AM4192C

Color code: White

3. DIMENSIONS (mm)

A	B	C	D
43.6	23.4	41	8.5

4. CONNECTION

Type of terminals: with screws

Terminal capacity: 1 x 2.5 mm²

Stripping length: 6 mm

Circuit Breaker: MAX. 16 A

Necessary safety precautions:

**Switch OFF the power at the main circuit breaker.
Make sure that the power is OFF before continuing
with the installation.**

5. TECHNICAL CHARACTERISTICS**5.1 Mechanical characteristics**

Impact tests: IK 04

Penetration by solid bodies/liquid: IP 40

5.2 Material characteristics

Base: PC V-0 class

Cover: PC V-0 class

Self-extinguishing:

850°C/30 s for insulating components holding live parts in place.

650°C/30 s for other insulating components.

5.3 Electrical characteristics

All values listed below are measured at an ambient temperature of + 20° and after 30 minutes of operation.

Nominal input voltage	100-240 V~
Nominal input frequency	50/60 Hz
Nominal input current	0.5 A
Nominal output current	3.0 A ^(*)
Output power	20 W
Nominal output voltage	5.0 V ^(*)
Average efficiency in active mode	86 %
Stand-by power consumption	< 0.05W
Consumption class without load and average level of efficiency: Level VI	
Protection class	II - Low voltage

(*) Optimise/voltage:

5.0 V \Rightarrow 3.0 A - 15 W

9.0 V \Rightarrow 2.2 A - 20 W

12.0 V \Rightarrow 1.6 A - 20 W

Note: To optimize the charging time of your device, ensure turn it off during the charging phase.

5.4 Climate characteristics

Storage temperature: -20°C to +70°C

Operating temperature: 5°C to +40°C

6. CLEANING

Surface cleaning with a cloth.

Do not use: acetone, tar remover, trichloroethylene.

Caution: Always test before using other special cleaning products

7. STANDARDS AND APPROVALS

Power Delivery certified product: open standard for fast charging via an exchange between the terminal and the charger.

Compliance with installation and manufacturing standards.
Refer to e-catalogue.