


USB universal charger - 1500 mA - Type A

Use


For recharging portable devices such as phones, smartphones, MP3 or MP4, loudspeakers, watches, game consoles, powerbanks.

Range

Designation	Item
USB charger with 1 type A port for charging electronic devices up to 7,5W (1,5A). - 100-240 V 50-60 Hz DIRECT power supply Output voltage 5V - 1 module	<input type="checkbox"/> RW4190A <input checked="" type="checkbox"/> RG4190A

Color code:

White colour Black colour

Overall Dimensions


A	B	C	D
45	22.5	41	9.8

Connection

Type of terminal: with screws
Terminal capacity: 1 x 2.5 mm²
Stripping length: 6 mm
Screwdriver: flat 3.5 mm

Recommended use: circuit terminal outlet

Technical Characteristics

- **Protection index** (considering a complete installation, including cover plate)
Penetration by solid bodies/liquid: IP20D

- **Mechanical characteristics**

Impact test: IK 04

Technical Characteristics (continued)

- Material characteristics

Material:

Case: PC (Polycarbonate) Key cover: ABS

Halogen free and UV resistant.

Self-extinguishing:

850° C / 30 s for insulating parts holding live parts in place

650° C / 30 s for other parts made of insulating materials

- Climatic characteristics

Storage temperature: - 10° C to + 70° C

Use temperature: - 5° C to + 35° C

- Electrical characteristics

All values listed below are measured at an ambient temperature of + 25° and after 15 minutes of operation.

Nominal input voltage	100 - 240 V~
Nominal input frequency	50-60 Hz
Maximum input current	250 mA
Maximum power consumption in standby	0.07W
Power average efficiency	81 %
Nominal output voltage	5 V ---
Maximum output current	1500 mA
Classe de consommation hors charge et niveau moyen d'efficacité: level VI*	
Safety-standard	EN 60950-1
Protection class	II - Low voltage

* NB: European Regulation No. 278/2009 of 6 April 2009, Directive 2005/32/EC on eco-design requirements for AC/DC power supplies

- Average charging time for devices equipped with lithium ion polymer batteries:

- 80 % charged < 1 h 15

- 100 % charged < 2 h 00

Cleaning

Clean the surface with a cloth.

Do not use: acetone, tar remover cleaning agents or trichlorethylene.

- **Caution: Always test before using special cleaning products.**

Standards and approvals

EC 60950-1: low voltage directive.

IEC 62684 / EN 50558 conform to the interoperability specifications of common external power supply (EPS) for use with mobile telephones.

Conform to eco design directive 2009/125/EC.