

## Bticino S.p.A.


Viale Borri, 231 – 21100 Varese (VA) – ITALY

Item codes: from 387870 to 387875

www.bticino.com - www.legrand.com

# **TILOK TKT connectors**

# Straight connectors pipe-pipe




SUMMARY	PAGES
1. Description and applications	1
2. Dimensions and compatibility	1
3. Technical features	1
4. Environmental profile	2
5. Conformity and approvals	2

### 1. DESCRIPTION AND APPLICATIONS

Straight metal patented connector with fast coupling system to connect two metal rigid pipes. Suitable for most applications it ensures the connection of pipes with high mechanical and thermal performances, high resistance to traction and torque and a good resistance to vibration. Used together with TAZ or TAIX conduits and it guarantees an IP68 protection index with a good tightening and a fast patented coupling system. It's the ideal solution for energy, signal or power distribution in industrial, commercial, infrastructures and residential applications.

## 2. DIMENSIONS AND COMPATIBILITY

## Dimensions and packaging:



Item TKT	Conduit	Dimensions [mm]			Pack
	diameter [mm]*	ØPU	СН	L	[pcs]
387870	16	14,0	24,0	49,0	10
387871	20	18,0	28,0	50,0	10
387872	25	22,6	33,0	53,0	5
387873	32	29,6	40,0	56,0	5
387874	40	37,6	50,0	60,0	3
387875	50	47,6	59,0	64,0	2

<sup>\*</sup> External diameter of the pipe

# Compatibility:

Conduits TAZ and TAIX series, metal accessories and equipments.





### Patent:

All the TILOK connectors have a patented quick system to be coupled with the rigid metal pipes. The patented quick system works without any tools and ensures a protection index IP68 (used with TAZ or TAIX conduits).



## 3. TECHNICAL FEATURES

#### Raw material:

Body: nickel plated brass UNI EN 12164 CW 614N with nickel plating 2  $\div$  5  $\mu m$ .

Gasket: Thermosetting elastomeric.

#### Resistance to corrosion:

Represents the resistance to corrosion in different environments: all TILOK connectors have been subjected to the corrosion tests.

Resistance to corrosion in neutral saline mist in according to UNI ISO 9227 (pluviometric index 1,8 ml/hours): no signs of corrosion after 192 hours.

Resistance to corrosion in constant dump humidity in according to DIN 50017 SK (conditions:  $38~^{\circ}\text{C}$  /  $100~^{\circ}\text{F}$  with 100% of relative humidity): no signs of corrosion after 1000 hours.

Technical data sheet: IDP000079EN/01 Updated: 30<sup>th</sup> October 2014 Created: 30<sup>th</sup> October 2014

# **TILOK TKT connectors**

# Straight connectors pipe-pipe

# Operating temperature:

Minimum: -25° C / -13° F Maximum: +150° C / +302° F

## Electric properties:

Electric continuity guaranteed.

### IP protection index:

IP68 with TAZ and TAIX series conduits.

1 <sup>st</sup> digit IP					
Protection against the ingress of solid bodies					
	No protection				
Ø 50 mm	Protection against solid bodies larger than 50 mm (e.g.: accidental contact)				
Ø 12.5 mm	Protection against solid bodies larger than 12 mm (e.g.: finger)				
(O)#2.5 mm	Protection against solid bodies larger than 2.5 mm				
( <u>)ø1</u> mm <b>/</b>	Protection against solid bodies larger than 1 mm				
0 !	Protection against dust				
0	Complete protection against dust				

2 <sup>nd</sup> digit IP				
Protection against the ingress of liquids				
0	Protection against drops of water falling at up to 15° from the vertical			
	Protection against drops of rain water at up to 60° from the vertical			
O	Protection against sprays of water from all directions			
	Protection against jets of water from all directions			
-01	6 Protection against jets of water of similar force to heavy seas			
	Protection against the effects of immersion			
E O	Protection against prolonged effects of immersion under pressure			

## 4. ENVIRONMENTAL PROFILE

All the items identified in this technical sheet respect in terms of concentration of substances and raw materials the European legislations about dangerous and forbidden substances and chemical preparations.

## 5. CONFORMITY AND APPROVALS



All the items identified in this technical sheet are compliant to all the requirements and the regulations currently in force in the European Union about safety, health and environmental issues.



IMQ mark: items from 387870 to 387875.



RINA mark: items from 387870 to 387875.

For technical documentation, test reports, commercial information or any other needs please refer to the local LEGRAND office.

Item codes: from 387870 to 387875

 **L7** legrand